

GEARWRENCH[®]

FORGE AHEAD



12 Point Long Pattern Combination Wrenches

Includes: SAE and Metric, Sets and Open Stock

**LIFETIME
WARRANTY**



12 Point Long Pattern Combination Wrenches



12 Point SAE/Metric Long Pattern Combination Sets

SKU #	Description	Includes	Sizes	Weight	
81919	44 Pc. 12 Point SAE/Metric Long Pattern Combination Wrench Set	SAE	1/4", 5/16", 11/32", 3/8", 7/16", 1/2", 9/16", 5/8", 11/16", 3/4", 13/16", 7/8", 15/16", 1", 1-1/16", 1-1/8", 1-1/4", 1-5/16", 1-1/2"	35.33 lb	
		Metric	6, 7, 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 20, 21, 22, 23, 24, 25, 26, 27, 28, 30, 32mm		
81900	24 Pc. 12 Point SAE/Metric Long Pattern Combination Wrench Set	SAE	1/2", 9/16", 5/8", 11/16", 3/4", 13/16", 7/8", 15/16", 1"	12.35 lb	
		Metric	8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 20, 21, 22mm		





12 Point Large Long Pattern Combination Sets

SKU #	Description	Includes	Sizes	Weight	
81921	5 Pc. 12 Point SAE Large Long Pattern Combination Wrench Set	SAE	1-1/16", 1-1/8", 1-1/4", 1-5/16", 1-1/2"	9.94 lb	
81922	5 Pc. 12 Point Metric Large Long Pattern Combination Wrench Set	Metric	25, 26, 27, 29, 30, 32mm	10.20 lb	


12 Point SAE Long Pattern Combination Sets

SKU #	Description	Includes	Sizes	Weight	
81901	15 Pc. 12 Point SAE Long Pattern Combination Wrench Set	SAE	1/4", 9/32", 5/16", 11/32", 3/8", 7/16", 1/2", 9/16", 5/8", 11/16", 3/4", 13/16", 7/8", 15/16", 1"	6.05 lb	
81917	18 Pc. 12 Point SAE Long Pattern Combination Wrench Set with Wrench Roll	SAE	1/4", 9/32", 5/16", 11/32", 3/8", 7/16", 1/2", 9/16", 5/8", 11/16", 3/4", 13/16", 7/8", 15/16", 1", 1-1/16", 1-1/8", 1-1/4"	12.40 lb	
81918	15 Pc. 12 Point SAE Long Pattern Combination Wrench Set with Wrench Roll	SAE	5/16", 3/8", 7/16", 1/2", 9/16", 5/8", 11/16", 3/4", 13/16", 7/8", 15/16", 1", 1-1/16", 1-1/8", 1-1/4"	12.83 lb	
81934	11 Pc. 12 Point SAE Long Pattern Combination Wrench Set with Wrench Roll	SAE	3/8", 7/16", 1/2", 9/16", 5/8", 11/16", 3/4", 13/16", 7/8", 15/16", 1"	5.84 lb	
81933	7 Pc. 12 Point SAE Long Pattern Combination Wrench Set with Wrench Roll	SAE	3/8", 7/16", 1/2", 9/16", 5/8", 11/16", 3/4"	2.76 lb	

12 Point Metric Long Pattern Combination Sets

SKU #	Description	Includes	Sizes	Weight	
81902	15 Pc. 12 Point Metric Long Pattern Combination Wrench Set	Metric	8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 20, 21, 22mm	9.55 lb	
81916	22 Pc. 12 Point Metric Long Pattern Combination Wrench Set with Wrench Roll	Metric	6, 7, 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 20, 21, 22, 23, 24, 27, 30, 32mm	13.90 lb	
81920	18 Pc. 12 Point Metric Long Pattern Combination Wrench Set with Wrench Roll	Metric	7, 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 20, 21, 22, 23, 24 mm	7.82 lb	
81932	9 Pc. 12 Point Metric Long Pattern Combination Wrench Set with Wrench Roll	Metric	7, 8, 9, 10, 11, 12, 13, 14, 15 mm	2.09 lb	

12 Point Long Pattern Combination Open Stock



SKU #	SAE Size	End A Width	End A Thickness	End B Width	End B Thickness	Overall Length	Wt. (lbs.)
81650	1/4"	0.52"	0.16"	0.45"	0.20"	5.09"	0.07
81651D	9/32"	0.57"	0.17"	0.48"	0.21"	5.44"	0.09
81652D	5/16"	0.65"	0.18"	0.54"	0.22"	5.80"	0.09
81653	11/32"	0.73"	0.19"	0.58"	0.244"	6.22"	0.11
81654	3/8"	0.81"	0.21"	0.63"	0.27"	6.54"	0.13
81655	7/16"	0.89"	0.24"	0.69"	0.30"	7.29"	0.18
81656	1/2"	1.05"	0.25"	0.78"	0.34"	8.11"	0.24
81657	9/16"	1.14"	0.27"	0.85"	0.37"	8.74"	0.26
81658	5/8"	1.29"	0.30"	0.94"	0.41"	9.52"	0.38
81659	11/16"	1.38"	0.32"	1.02"	0.43"	10.23"	0.49
81660	3/4"	1.55"	0.36"	1.09"	0.48"	10.97"	0.53
81661	13/16"	1.70"	0.39"	1.20"	0.52"	11.83"	0.73
81662	7/8"	1.78"	0.41"	1.26"	0.54"	12.52"	0.82
81663	15/16"	1.95"	0.43"	1.38"	0.58"	13.25"	1.04
81664	1"	2.02"	0.45"	1.40"	0.60"	14.04"	1.15
81733	1-1/16"	2.22"	0.47"	1.53"	0.65"	14.75"	1.43
81734	1-1/8"	2.47"	0.50"	1.69"	0.70"	16.00"	1.85
81749	1-5/16"	3.10"	0.61"	2.19"	0.93"	18.74"	2.22
81750	1-1/2"	3.10"	0.61"	2.19"	0.93"	19.72"	2.25
81815	1-3/16"	2.48"	0.49"	1.76"	0.74"	16.22"	1.60
81735	1-1/4"	2.63"	0.52"	1.81"	0.72"	16.00"	2.18
81816	1-3/8"	2.81"	0.53"	2.05"	0.87"	19.96"	2.82
81817	1-7/16"	3.03"	0.63"	2.15"	0.87"	21.10"	3.60
81818*	1-5/8"	3.40"	0.67"	2.43"	0.96"	24.09"	5.41
81819*	1-11/16"	3.40"	0.67"	2.43"	0.96"	24.09"	5.34
81820*	1-3/4"	3.69"	0.78"	2.62"	0.98"	25.55"	5.92
81821*	1-13/16"	3.69"	0.78"	2.62"	0.98"	25.55"	5.81
81822*	1-7/8"	3.90"	0.75"	2.76"	1.06"	27.09"	7.04
81823*	2"	4.02"	0.75"	2.87"	1.06"	27.13"	7.08
81824*	2-1/16"	4.00"	0.75"	2.87"	1.06"	27.09"	6.95
81825*	2-1/8"	4.41"	0.84"	3.17"	1.13"	27.80"	9.71
81826*	2-3/16"	4.41"	0.84"	3.17"	1.13"	27.80"	9.54
81827*	2-1/4"	4.41"	0.84"	3.17"	1.13"	27.80"	9.44
81828*	2-3/8"	4.99"	0.94"	3.67"	1.32"	29.84"	13.23
81829*	2-1/2"	4.99"	0.94"	3.67"	1.32"	29.84"	13.10
81830*	2-9/16"	5.43"	1.00"	4.06"	1.48"	31.89"	18.92
81831*	2-5/8"	5.43"	1.00"	4.02"	1.50"	31.89"	19.03
81832*	2-3/4"	5.39"	1.00"	4.06"	1.50"	31.89"	18.08

SKU #	Metric Size	End A Width	End A Thickness	End B Width	End B Thickness	Overall Length	Wt. (lbs.)
81736	6mm	0.52"	0.16"	0.45"	0.20"	5.09"	0.07
81737	7mm	0.57"	0.17"	0.48"	0.21"	5.45"	0.07
81665	8mm	0.65"	0.18"	0.54"	0.22"	5.80"	0.09
81666	9mm	0.73"	0.19"	0.58"	0.244"	6.22"	0.11
81667	10mm	0.81"	0.21"	0.63"	0.27"	6.54"	0.13
81668	11mm	0.89"	0.24"	0.69"	0.30"	7.29"	0.18
81669	12mm	0.97"	0.24"	0.73"	0.33"	7.74"	0.18
81670	13mm	1.05"	0.25"	0.78"	0.34"	8.11"	0.30
81671	14mm	1.14"	0.28"	0.85"	0.37"	8.74"	0.32
81672	15mm	1.21"	0.29"	0.89"	0.39"	9.13"	0.35
81673	16mm	1.29"	0.30"	0.94"	0.41"	9.52"	0.40
81674	17mm	1.38"	0.32"	1.02"	0.43"	10.23"	0.43
81675	18mm	1.461"	0.34"	1.05"	0.45"	10.60"	0.49
81676	19mm	1.55"	0.36"	1.08"	0.47"	10.97"	0.54
81677	20mm	1.65"	0.38"	1.11"	0.49"	11.40"	0.62
81678	21mm	1.70"	0.40"	1.14"	0.51"	11.83"	0.68
81679	22mm	1.78"	0.41"	1.26"	0.54"	12.52"	0.69
81741	23mm	1.87"	0.42"	1.29"	0.56"	12.75"	0.99
81742	24mm	1.95"	0.43"	1.33"	0.58"	13.25"	1.00
81751	25mm	2.02"	0.45"	1.40"	0.60"	14.04"	1.10
81752	26mm	2.14"	0.45"	1.47"	0.62"	14.33"	1.12
81743	27mm	2.22"	0.47"	1.53"	0.65"	14.75"	1.38
81753	28mm	2.47"	0.50"	1.69"	0.70"	16.00"	1.89
81809	29mm	2.34"	0.47"	1.67"	0.67"	15.39"	1.25
81744	30mm	2.56"	0.52"	1.69"	0.72"	17.00"	2.12
81745D	32mm	2.63"	0.52"	1.81"	0.72"	17.36"	2.13
81840*	36mm	2.81"	0.53"	2.01"	0.85"	19.96	2.73
81841*	41mm	3.40"	0.67"	2.43"	0.96"	24.09	5.36
81842*	46mm	3.69"	0.78"	2.62"	0.98"	25.55	5.81
81843*	50mm	3.90"	0.75"	2.87"	1.06"	26.97	7.08
81844*	55mm	4.41"	0.84"	3.17"	1.13"	27.80	9.65
81845*	60mm	4.99"	0.94"	3.67"	1.32"	29.84	13.26
81846*	65mm	5.47"	1.00"	4.06"	1.50"	31.89	19.05
81847*	70mm	5.39"	1.00"	4.06"	1.50"	31.89	18.22

*Satin Finish