

# Han 3A-HBM-SL-C cap with seal



Part number	09 20 003 0306
Specification	Han 3A-HBM-SL-C cap with seal
HARTING eCatalogue	https://b2b.harting.com/09200030306

Image is for illustration purposes only. Please refer to product description.

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han A <sup>®</sup>
Type of hood/housing	Bulkhead mounted housing
Description of hood/housing	Straight With metal cover With seal

#### Version

Locking type	Single locking lever
Size	3 A
Field of application	Standard Hoods/housings for industrial applications
Details	for female inserts

## Technical characteristics

Limiting temperature	-40 +125 °C
Degree of protection acc. to IEC 60529	IP44 IP65 / IP67 with seal screw 09 20 000 9918
Type rating acc. to UL 50 / UL 50E	12

## Material properties

Material (hood/housing)	Zinc die-cast	
Surface (hood/housing)	Powder-coated	
Colour (hood/housing)	RAL 7037 (dust grey)	
Material (seal)	NBR	



### Material properties

Material (locking)	Steel
Surface (locking)	Zinc plated
RoHS	compliant with exemption
RoHS exemptions	6(a) / $6(a)$ -I: Lead as an alloying element in steel for machining purposes and in galvanised steel containing up to 0,35 % lead by weight / Lead as an alloying element in steel for machining purposes containing up to 0,35 % lead by weight and in batch hot dip galvanised steel components containing up to 0,2 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

## Specifications and approvals

Approvals	DNV GL
CE	Yes

#### Commercial data

Packaging size	10
Net weight	50 g
Country of origin	Romania
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors

# **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HARTING: 09200030306