


Deep groove ball bearings, single row, seal on both sides

Principal dimensions			Basic load ratings		Fatigue load limit P_u	Speed ratings		Mass	Designation
d	D	B	dynamic	static		Reference speed	Limiting speed		
mm			kN		kN	r/min		kg	-
12	32	10	7,28	3,1	0,132	-	15000	0,037	6201-2RSH *



Calculation factors

$k_r = 0,025$

$f_0 = 12$