

016H6703

Pressostat 016H6703

016 are simple mechanical pressostats for high or low pressure, equipped with a simple contact SPDT closed or opened according to the increase or to the decline of pressure.

These devices are available in automatic rearmament or with a button of manual rearmament.

The point of order is adjustable by saw.

The difference is adjustable only for the version with automatic rearmament.

The models having the certification TUV contain a double bellows to prevent every risk of flight of cooler.

In standard version pressostats is supplied with joins flare male.

Certain versions contain capillaries (from 1m of length) equipped with flares nuts females.

Other versions are supplied with a stiff tube to be brazed.

The models with manual rearmament are IP33 whereas the models with automatic rearmament are IP44.

TECHNICAL DATA:

- Scale of unit : bar and Psi
- Connections gas: 1/4 " flare male
- to Be able to of cut: 16A inductive in 250V on the main contact (NO. or NF) and 1A inductive in 250V on the opposite contact
- These devices are in accordance with the standards EN60730-2-6 and EN60730-2-9 and made according to the standard ISO9001
- connection: border 1: common, border 2: opened to the increase, the border 4: closed in the increase
- Equipped of one press étoupe of 14 mm
- Compatibility with any sorts of gas
- Assembly : 2 pre-drillings behind the pressostat for the insertion of saw M4x6mm (Supplied).