

Telemecanique Sensors

1875 Founders Drive

Dayton, OH 45420-4017

Toll Free: (800) 435-2121 • Phone: (937) 252-2121 • Fax: (937) 258-5830

E-Mail: hydepark@us.schneider-electric.com • Web site: www.sesensors.com

Item # VM18PNOQ, Ultrasonic Sensor, Discrete, 18 mm Barrel, 12-24 VDC

List Price QUOTE

Ultrasonic Sensor, Discrete, 18 mm Barrel, 12-24 VDC

- Discrete proximity, analog or dual-level sensing
- UL, CE, RoHS

SPECIFICATIONS

Diameter	18 mm
Length	77.62 mm 3.05 in
Width	18.0 mm 0.71 in
Depth	18 mm 0.71 in
Face Material	Glass Epoxy
Body Style	Barrel
Volts Type	DC
Voltage Range	12-24 VDC
Current Consumption	40 mA
Circuit Type	Normally Open
Output Mode	PNP
Temp Range	-30° to 70° C (-22° to 158° F)
Max Load	100 mA
Sensing Range	50.8 to 508 mm (2.0 to 20.0 in)

Response Time	15 ms
Sonic Frequency	300 Hz
Field Configurable	No
DeviceNet	No
NEMA Type	4X (indoor use only)
Connector Type	M12
Standards	UL, CE Rohs
Special Features	Tamper Proof with PB100 Pushbutton Accessory
IP Rating	IP67