



## Heyco® Snap Latch Rivets

### Grommet

- Designed for fast and easy installation and removal - simply push to fasten and pull to release.
- Ideal for frequent maintenance work.
- Typical applications include metal enclosures, telecom equipment, appliances and electrical equipment.

FIXED PANEL HOLE DIAMETER		REMOVABLE PANEL THICKNESS		PART NO.		DESCRIPTION	MATING PLUNGER		PART DIMENSIONS					
in.	mm.	in.	mm.	Black	White		Black	White	A Body Length		B Head Diameter		C Head Height	
								in.	mm.	in.	mm.	in.	mm.	
.253	6,4	.043	1,1	<b>12283</b>	<b>12284</b>	HSLG-1M	12261	12262	.31	8,0	.33	8,5	.07	1,8
		.063	1,6	<b>12285</b>	<b>12286</b>	HSLG-2M	12263	12264	.33	8,5				
		.098	2,5	<b>12287</b>	<b>12288</b>	HSLG-3M	12265	12266	.37	9,5				
		.161	4,1	<b>12289</b>	<b>12290</b>	HSLG-4M	12267	12268	.43	11,0				
.319	8,1	.043	1,1	<b>17000</b>	<b>17000W</b>	HSLG-SL	17005	17005W	.34	8,6	.43	10,8	.08	2,0
		.063	1,6	<b>17001</b>	<b>17001W</b>	HSLG-1L	17006	17006W	.35	9,0				
		.098	2,5	<b>17002</b>	<b>17002W</b>	HSLG-2L	17007	17007W						
		.161	4,1	<b>17003</b>	<b>17003W</b>	HSLG-3L	17008	17008W	.39	10,0				
		.209	5,3	<b>17004</b>	<b>17004W</b>	HSLG-4L	17009	17009W	.46	11,7				
		.209	5,3	<b>17004</b>	<b>17004W</b>	HSLG-4L	17010	17010W	.51	12,9				

**NEW!**

Standard colors black and white.

### Plunger

REMOVABLE PANEL HOLE DIAMETER	ASSEMBLED PANEL THICKNESS RANGE				PART NO.		DESCRIPTION	PLUNGER STYLE		MATING GROMMET		
	Minimum	Maximum	Black	White	Fig.	Alt.		Black	White			
in. mm.	in. mm.	in. mm.	in. mm.	Black	White							
.237	6,0	.059	1,5	.146	3,7	<b>12261</b>	<b>12262</b>	HSLPB-1M	4	N/A	12283	12284
		.079	2,0	.165	4,2	<b>12263</b>	<b>12264</b>	HSLPB-2M	4		12285	12286
		.118	3,0	.205	5,2	<b>12265</b>	<b>12266</b>	HSLPB-3M	4		12287	12288
		.181	4,6	.272	6,9	<b>12267</b>	<b>12268</b>	HSLPB-4M	4		12289	12290
.299	7,6	.059	1,5	.146	3,7	<b>17005</b>	<b>17005W</b>	HSLPL-SL	1	3	17000	17000W
		.079	2,0	.165	4,2	<b>17006</b>	<b>17006W</b>	HSLPL-1L	1	3	17001	17001W
		.118	3,0	.205	5,2	<b>17007</b>	<b>17007W</b>	HSLPL-21L	2	3		
		.181	4,6	.272	6,9	<b>17008</b>	<b>17008W</b>	HSLPL-2L	1	3	17002	17002W
		.228	5,8	.315	8,0	<b>17009</b>	<b>17009W</b>	HSLPL-3L	1	3	17003	17003W
		.228	5,8	.315	8,0	<b>17010</b>	<b>17010W</b>	HSLPL-4L	1	3	17004	17004W

**NEW!**

Standard colors black and white.

Fig. 1



Fig. 2



Fig. 3










Fig. 1

Fig. 2

Fig. 3 (Alternate)

Fig. 4

*Quick Specs*

Material Nylon 6  
 Flammability Rating 94V-2  
 Temperature Range -40°F (-40°C) to 239° F (115°C)