



	Cable Type	Diameter A	Diameter B	For Cable Diameter
5155 Series	RG 58, 141	.23 (5,84) x .51 (12,95) Deep	.21 (5,33)	.185" - .200"
5156 Series	RG 59, 62, 210	.28 (7,11) x .26 (6,60) Deep	.26 (6,60)	.237" - .247"
5157 Series	RG 174, 187, 188	.160 (4,06) x .51 (12,95) Deep	.12 (3,05)	.090" - .110"

MATERIALS:

PVC

Marking: "POMONA ELECTRONICS"

RATINGS:

Operating Temperature: +50C°. (+122°F.) Max.

ORDERING INFORMATION: Model 5155-*, 5156-*, 5157-*

*=Color Code, -0 Black, -1 Brown, -2 Red, -3 Orange, -4 Yellow, -5 Green, -6 Blue, --7 Violet, -8 Gray, -9 White

Sold in packages of 10

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ± .005" (.127 mm).
 All specifications are to the latest revisions. Specifications are subject to change without notice.
 Registered trademarks are the property of their respective companies.

Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[5156-0](#) [5156-2](#) [5155-2](#) [5155-0](#) [5157-0](#) [5156-0#](#) [5155-0#](#) [5157-0#](#)