

FL SFP SX2 - Media module



2702397

<https://www.phoenixcontact.com/us/products/2702397>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.

Gigabit SFP module for transmission up to 2 km with a wavelength of 1310 nm.



Product Description

SFP module with a data transmission speed of 1000 Mbps, a wavelength of 1310 nm, and a maximum transmission length of 2 km.

Your advantages

- MSA compliant

Commercial Data

Item number	2702397
Packing unit	1 pc
Minimum order quantity	1 pc
Sales Key	DN22
Product Key	DNN1ZS
Catalog Page	Page 332 (C-6-2019)
GTIN	4055626163161
Weight per Piece (including packing)	29.9 g
Weight per Piece (excluding packing)	29.9 g
Customs tariff number	85176200
Country of origin	TW

FL SFP SX2 - Media module



2702397

<https://www.phoenixcontact.com/us/products/2702397>

Technical Data

Dimensions

Width	13.7 mm
Height	8.95 mm
Length	56.5 mm

Material specifications

Housing material	Metal
------------------	-------

Mounting

Mounting type	Insert in SFP slot
---------------	--------------------

Interfaces

Ethernet FO

Connection method	LC
Transmission speed	1 Gbps
Transmit capacity, minimum	-15 dBm
Transmit capacity, maximum	-1 dBm
Minimum receiver sensitivity	-23 dBm
Maximum receiver sensitivity	-3 dBm
Transmission physics	multi-mode fiberglass
Transmission length	2 km (Fiberglass 50/125) 1 km (Fiberglass 62.5/125)
Wavelength	1310 nm
Signal LEDs	depending on the Factoryline device
No. of channels	1 (LC multi-mode)
Transmit capacity, minimum	-15 dBm
Transmit capacity, maximum	-1 dBm
Minimum receiver sensitivity	-3 dBm
Maximum receiver sensitivity	-23 dBm
Transmission physics	multi-mode fiberglass

Product properties

Type	Factoryline devices with SFP slot
Product type	SFP module
MTTF	1862 Years (Telcordia SR-332, temperature factor at 40°C = 1, stress factor at 50% = 1, environmental factor = 1)
Format	SFP (Small Form-factor Pluggable)

LED signaling

Status display	via a Factoryline device
----------------	--------------------------

Electrical properties

FL SFP SX2 - Media module



2702397

<https://www.phoenixcontact.com/us/products/2702397>

Maximum power dissipation for nominal condition	1 W
Transmission medium	FO

Supply

Supply voltage	3.3 V (via Factoryline switch)
Power supply connection	via SFP slot
Max. current consumption	300 mA
Current consumption	300 mA

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 75 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C (non-condensing)
Case temperature	max. 85 °C (Operation)

FL SFP SX2 - Media module



2702397

<https://www.phoenixcontact.com/us/products/2702397>

Approvals



DNV GL

Approval ID: TAA00000YV



LR

Approval ID: LR22250919TA



NK

Approval ID: TA19464M



BV

Approval ID: 48146/A1 BV

BSH

Approval ID: Nr. 966



RINA

Approval ID: ELE162721XG

ABS

Approval ID: 21-2066186-PDA

FL SFP SX2 - Media module



2702397

<https://www.phoenixcontact.com/us/products/2702397>

Classifications

ECLASS

ECLASS-9.0	19179290
ECLASS-10.0.1	19179290
ECLASS-11.0	19179090
ECLASS-12.0	19179090
ECLASS-13.0	19179090

ETIM

ETIM 8.0	EC000310
----------	----------

UNSPSC

UNSPSC 21.0	43222600
-------------	----------

FL SFP SX2 - Media module

2702397

<https://www.phoenixcontact.com/us/products/2702397>



Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

FL SFP SX2 - Media module



2702397

<https://www.phoenixcontact.com/us/products/2702397>


Accessories

FOC-LC:PA-SC:PA-OM2:D01/1 - FO patch cable

1115607

<https://www.phoenixcontact.com/us/products/1115607>

Multi-mode OM2 duplex jumper, LC-SC, UPC polishing, length 1 m




FOC-LC:PA-SC:PA-OM2:D01/2 - FO patch cable

1115605

<https://www.phoenixcontact.com/us/products/1115605>

Multi-mode OM2 duplex jumper, LC-SC, UPC polishing, length 2 m



FL SFP SX2 - Media module

2702397

<https://www.phoenixcontact.com/us/products/2702397>




FOC-SC:PA-SC:PA-OM4:D01/2 - FO patch cable

1115423

<https://www.phoenixcontact.com/us/products/1115423>

Multi-mode OM4 duplex jumper, SC-SC, UPC polishing, length 2 m




FOC-SC:PA-SC:PA-OM4:D01/1 - FO patch cable

1115424

<https://www.phoenixcontact.com/us/products/1115424>

Multi-mode OM4 duplex jumper, SC-SC, UPC polishing, length 1 m



FL SFP SX2 - Media module

2702397

<https://www.phoenixcontact.com/us/products/2702397>




FOC-LC:PA-ST:PA-OM2:D01/2 - Fiber optic cable

1115587

<https://www.phoenixcontact.com/us/products/1115587>

Multi-mode OM2 duplex jumper, LC-ST, UPC polishing, length 2 m




FOC-LC:PA-ST:PA-OM2:D01/1 - Fiber optic cable

1115588

<https://www.phoenixcontact.com/us/products/1115588>

Multi-mode OM2 duplex jumper, LC-ST, UPC polishing, length 1 m



FL SFP SX2 - Media module

2702397

<https://www.phoenixcontact.com/us/products/2702397>




FOC-LC:PA-SC:PA-OM4:D01/2 - FO patch cable

1115600

<https://www.phoenixcontact.com/us/products/1115600>

Multi-mode OM4 duplex jumper, LC-SC, UPC polishing, length 2 m




FOC-LC:PA-SC:PA-OM4:D01/1 - FO patch cable

1115601

<https://www.phoenixcontact.com/us/products/1115601>

Multi-mode OM4 duplex jumper, LC-SC, UPC polishing, length 1 m



FL SFP SX2 - Media module

2702397

<https://www.phoenixcontact.com/us/products/2702397>




FOC-LC:PA-LC:PA-OM4:D01/2 - FO patch cable

1115624

<https://www.phoenixcontact.com/us/products/1115624>

Multi-mode OM4 duplex jumper, LC-LC, UPC polishing, length 2 m




FOC-LC:PA-LC:PA-OM4:D01/1 - FO patch cable

1115625

<https://www.phoenixcontact.com/us/products/1115625>

Multi-mode OM4 duplex jumper, LC-LC, UPC polishing, length 1 m



FL SFP SX2 - Media module

2702397

<https://www.phoenixcontact.com/us/products/2702397>




FOC-LC:PA-LC:PA-OM2:D01/1 - FO patch cable

1115633

<https://www.phoenixcontact.com/us/products/1115633>

Multi-mode OM2 duplex jumper, LC-LC, UPC polishing, length 1 m




FOC-LC:PA-LC:PA-OM2:D01/2 - FO patch cable

1115634

<https://www.phoenixcontact.com/us/products/1115634>

Multi-mode OM2 duplex jumper, LC-LC, UPC polishing, length 2 m



Phoenix Contact 2023 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com