



part no.		ØD	wire gauge		stripping length	Recommended Hand Crimp Tool	Note
silver plated	gold plated		mm <sup>2</sup>	AWG			
09 15 000 6207	09 15 000 6227	0,90	0,14-0,37	26-22	8	09 99 000 0888 09 99 000 0001	*only for four indent crimping tool adjusting Ø0,1
09 15 000 6204	09 15 000 6224	0,90	0,14-0,37	26-22		09 99 000 0110 09 99 000 0021	
09 15 000 6203	09 15 000 6223	1,10	0,5	20		09 99 000 0888 09 99 000 0001	
09 15 000 6205	09 15 000 6225	1,30	0,75	18		09 99 000 0110 09 99 000 0021	
09 15 000 6202	09 15 000 6222	1,45	1	18			
09 15 000 6201	09 15 000 6221	1,75	1,5	16			
09 15 000 6206	09 15 000 6226	2,25	2,5	14	6	09 99 000 0888 09 99 000 0001	



All Dimensions in mm  
Original Size DIN A4

Scale  
2:1

Free size tol.

Ref.

Sub.



All rights reserved

Department EL PD - DE

Created by  
RULLKOETTER

Inspected by  
SCHNIEDER

Standardisation  
RUETERA

Date  
2018-05-29

State  
Final Release

Title  
Han D crimp contacts female

Doc-Key / ECM-Nr.  
100109246/UGD/004/B  
500000135752

HARTING Electric GmbH & Co. KG  
D-32339 Espelkamp

Type  
TB

Number  
09 15 000 62XX

Rev.  
B

Page  
1/1