



## Electrical Commercial and Industrial

- [Products](#)
- [Documentation & Literature](#)
- [News & Tradeshows](#)
- [Support](#)

United States > All 3M Products > Energy > Electrical Commercial and Industrial > Products > Product Catalog

- [Find An Account Rep](#)
- [Where To Buy \(Find A Distributor\)](#)
- [Contact Us](#)

Electrical Commercial & Industrial Products Catalog > Electrical Tape, Mastics & Special Use > Vinyl Electrical Tapes > Scotch® Super 33+™ Vinyl Electrical Tape, 3/4 in x 20 ft (19 mm x 6,1 m), 100 per case

# Scotch® Super 33+™ Vinyl Electrical Tape, 3/4 in x 20 ft (19 mm x 6,1 m), 100 per case

3M ID 80610833800 UPC# 00054007061304 Part Number 33+SUPER-3/4X20FT



Scotch® Vinyl Electrical Tape 33 is a quality, general-purpose vinyl insulating tape. It has excellent resistance to: abrasion, moisture, alkalis, acid, copper corrosion and varying weather conditions.

[Buy at Shop3M.com](#)

**Need Help?**

**Questions?** We can help. [Contact Us](#)

### Overview |

Scotch® Super 33+™ Electrical Tape a black, 7 mil tape, on a 1 inch core, combines the flexibility of a PVC backing with excellent electrical insulating properties to provide primary electrical insulation for splices up to 600V. Abrasion-, corrosion-, and UV-resistant, it makes an excellent protective jacketing for high-voltage cables and wire harnessing. UL Listed and CSA Certified, it resists alkalis and acids, and is flame-retardant. Excellent all-weather performance in cold to 0(deg)F (-18(deg)C) or hot to 220(deg)F (105(deg)C).

### Specifications

<b>Adhesive Material</b>	Rubber Resin
<b>Agency Approvals</b>	CSA, UL Listed
<b>Application/Industry</b>	Industrial Construction, Residential Construction, Maintenance and Repair Operations, Communications, Automotive and Marine, Irrigation, Commercial Construction, Mining, Appliance and Fixture, Wind Power, Solar, Utility
<b>Backing Material</b>	Polyvinyl Chloride
<b>Breaking Strength</b>	15 lb/in
<b>Color</b>	Black
<b>Dielectric Strength</b>	1150 V/mil
<b>Family</b>	Scotch® Super 33+™ Vinyl Electrical Tape
<b>Insulated</b>	Yes
<b>Length</b>	20 Linear Foot
<b>Length (Metric)</b>	6.1 m
<b>Material</b>	PVC
<b>Operating Temperature Range (Celsius)</b>	-18 to 105 Degree Celsius
<b>Operating Temperature Range (Fahrenheit)</b>	0 to 220 Degree Fahrenheit
<b>Product Family</b>	Scotch® Super 33+™ Vinyl Electrical Tape
<b>Product Type</b>	Vinyl Tape
<b>RoHS 2011/65/EU Compliant</b>	Yes
<b>RoHS EU Comments</b>	RoHS 2011/65/EU compliant without exemption *Important RoHS information
<b>Rolls per Carton</b>	10
<b>Rolls per Case</b>	100
<b>Self-Extinguishing</b>	Yes
<b>Self Sticking/Amalgamating</b>	No
<b>Suitable for High Voltage</b>	No
<b>Tape Grade</b>	Premium
<b>Tape Type</b>	Vinyl
<b>Thickness</b>	7 mil
<b>Thickness (Metric)</b>	0.177 mm
<b>Trademark</b>	Scotch
<b>UV Resistant</b>	Yes
<b>Voltage Application</b>	Low Voltage
<b>Vulcanizing</b>	No
<b>Width</b>	0.75 Inch
<b>Width (Metric)</b>	19 mm

Manufacturing Origin: USA

The designation that a product is Manufactured in the USA means the product undergoes substantial transformation in one of our U.S. Manufacturing plants. Some products contain imported components.

Note: 3M products offered on a government contract that require country of origin representation must be certified by 3M Trade Compliance. Contact customer service at 800-245-3573 to request a certificate.

