



Vinyl Insulated Spade Terminals

159-1207, 159-1208, 159-1620, 159-1626
159-1628, 159-2220, 159-2226, 159-2228



Vinyl Insulated Spade Terminals



Dimensions: In.

SPECIFICATIONS	
Material thickness:	.032 inch
Material:	copper
Insulation:	vinyl

Mouser Stock No.	Wire Range (AWG)	Stud Size	Dimensions (In.)						Color
			W	L	F	B	D	C	
159-1207	12 - 10	8	.354	.941	.295	.492	.220	.134	Yellow
159-1208	12 - 10	10	.354	.941	.295	.492	.220	.134	Yellow
159-1620	16 - 14	10	.374	.835	.255	.394	.158	.091	Blue
159-1626	16 - 14	6	.236	.835	.255	.394	.158	.091	Blue
159-1628	16 - 14	8	.283	.835	.255	.394	.158	.091	Blue
159-2220	22 - 16	10	.374	.835	.255	.394	.134	.067	Red
159-2226	22 - 16	6	.252	.835	.255	.394	.134	.067	Red
159-2228	22 - 16	8	.283	.835	.255	.394	.134	.067	Red

159-1207, 159-1208, 159-1620, 159-1626
159-1628, 159-2220, 159-2226, 159-2228

Date Last Revised: 6-23-05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-300741

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[159-1620](#) [159-1628](#) [159-1626](#) [159-2226](#) [159-2228](#) [159-1207](#) [159-1208](#)