

Data sheet

LEDX20FLBN

Light / LED Wide Beam Lighting

LEDX20FLBN

20W LED Wide Angle Floodlight – Black



Features & Benefits

- Rust resistant Floodlight
- 316 stainless steel bracket and screws
- Marine grade aluminium heat sink
- Polycarbonate body and reflector
- Longlife – up to 30,000 hours for low maintenance
- Easy quick fit bracket installation

Technical Data

Operating Voltage	230V AC
Frequency	50Hz
Installation Type	Bracket Mounted
Earth Class Rating	Class I
Operating Temperature	-10°C to 40°C
Ingress Protection Rating	IP55
Wattage	20
Beam Angle	110° x 100°
Pan & Tilt Adjustment	110° Tilt (Floodlight)
Energy Efficiency	Class E
Energy Usage	21kWh/1000H
Lumen output (lm)	2000

Data sheet

LEDX20FLBN

Light / LED Wide Beam Lighting

Colour Temperature (K)	4000
LED Type	SMD (Intergrated)
Mounting Hole Centres (mm)	70
Multiple Unit Support	Yes
Cable Entry(s)	Side Entry (Grommet)

General

Weight (g)	550
Height (mm)	117
Width (mm)	174
Depth (mm)	97 (Inc Bracket 151)
Body Construction	Polycarbonate (Bracket 316 Stainless Steel, including screws)
Product Colour	Black
Accessories (Included)	Fittings (Rawl Plugs, Screws)
EAN Number	5012483014912
Guarantee Period	3 Years

Line Diagrams

