

SLFM360N

PIR Presence Detector (Flush Mount)

Features & Benefits

- Slimline sensor head design
- 360° detection zone for optimum coverage
- IP44 weatherproof rating (internal use only)
- Manual override (Pulse) for extended light on times
- Adjustable time setting
- Adjustable LUX setting
- 75mm diameter ceiling cut-out



Technical Data

Operating Voltage	230V AC
Frequency	50Hz
Installation Type	Flush Mount
Earth Class Rating	Class II
Operating Temperature	0°C to 40°C
Ingress Protection Rating	IP44
Setting Type	Dial
Max Mounting Height (Mtr)	2.5
Presence Detection (Mtr)	4
Motion Detection (Mtr)	8
Detection Angle	360°

Data sheet

SLFM360N

Light / PIR Presence Detectors

Hole Cut-Out Size (mm)	75
Standby Consumption	<0.5W
Number of Channels	1
Switch rating	250W LED, 2000W Halogen, 500W Fluorescent
ON Time Adjustment	3 Seconds to 18 Minutes. User Adjustable
Lux Level	1 to 1000
Detection Range (Mtr)	8
Permanent ON Facility	Yes (Pulse Override)
Dusk Till Dawn	No
Multiple Unit Support	Yes (Up to 8 In Parallel)
Cable Entry(s)	Back Entry

General

Weight (g)	90
Height (mm)	90
Width (mm)	90
Depth (mm)	60
Body Construction	Polycarbonate
Product Colour	White
Accessories (Included)	Terminal Cover
EAN Number	5012483014790
Guarantee Period	3 Years

Line Diagrams

