



preci-dip

WWW.PRECIDIP.COM TEL +41 32 421 04 00 SALES@PRECIDIP.COM

# PIN CONNECTORS 2.54 mm

CONNECTING PIN Ø 0.47 mm / SINGLE ROW / DOUBLE ROW  
SOLDER TAIL / RIGHT ANGLE

Right angle pin connectors, solder tail.


## TECHNICAL SPECIFICATIONS (FOR GENERAL SPECS, SEE PAGE 43)

INSULATOR	Black glass filled polyester PCT-GF30-FR
FLAMMABILITY	UL 94V-0
CONTACT	Brass CuZn36Pb3 (C36000)
CONNECTING PIN Ø	0.47 mm
MECHANICAL LIFE	Min. 500 cycles
RATED CURRENT	3 A
DIELECTRIC STRENGTH	Min. 1'000 V <sub>RMS</sub>

For corresponding socket connectors, see pages 69-84.

## ORDERING INFORMATION ROHS COMPLIANT PARTS

PP PLATING CODE	TERMINATION	CONNECTING PIN
10	0.25 µm gold	0.25 µm gold
80	Tin	Tin
V3	Tin	0.75 µm gold




Other plating on request (see page 178 for plating specs).

**NN number of poles.** Replace **NN** with the requested number of poles, e.g. 499-10-2**NN**-10-009101 for a double row version with 8 pins becomes 499-10-2**08**-10-009101.

### 399-PP-1NN-10-009101

Right angle pin connector, solder tail, single row


AVAILABILITY FROM 2 to 64 contacts  
(standard number of contacts: 64)



### 499-PP-2NN-10-009101

Right angle pin connector, solder tail, double row

AVAILABILITY FROM 4 to 72 contacts  
(standard number of contacts: 72)



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Preci-dip:

[399-83-164-10-003101](#) [383-10-120-00-001101](#) [383-10-156-00-001101](#) [383-10-119-00-001101](#) [383-10-130-00-001101](#) [383-10-129-00-001101](#) [383-10-128-00-001101](#) [383-10-160-00-001101](#) [383-10-159-00-001101](#) [383-10-158-00-001101](#) [383-10-157-00-001101](#) [383-10-155-00-001101](#) [383-10-164-00-001101](#) [383-10-163-00-001101](#) [383-10-162-00-001101](#) [383-10-161-00-001101](#) [383-10-108-00-001101](#) [383-10-105-00-001101](#) [383-10-104-00-001101](#) [383-10-103-00-001101](#) [383-10-102-00-001101](#) [383-10-107-00-001101](#) [383-10-137-00-001101](#) [383-10-136-00-001101](#) [383-10-135-00-001101](#) [383-10-134-00-001101](#) [383-10-106-00-001101](#) [383-10-145-00-001101](#) [383-10-132-00-001101](#) [383-10-142-00-001101](#) [383-10-141-00-001101](#) [383-10-140-00-001101](#) [383-10-139-00-001101](#) [383-10-138-00-001101](#) [383-10-149-00-001101](#) [383-10-148-00-001101](#) [383-10-147-00-001101](#) [383-10-146-00-001101](#) [383-10-131-00-001101](#) [383-10-144-00-001101](#) [383-10-143-00-001101](#) [383-10-154-00-001101](#) [383-10-153-00-001101](#) [383-10-152-00-001101](#) [383-10-151-00-001101](#) [383-10-150-00-001101](#) [383-10-113-00-001101](#) [383-10-112-00-001101](#) [383-10-111-00-001101](#) [383-10-110-00-001101](#) [383-10-109-00-001101](#) [383-10-121-00-001101](#) [383-10-133-00-001101](#) [383-10-118-00-001101](#) [383-10-117-00-001101](#) [383-10-116-00-001101](#) [383-10-115-00-001101](#) [383-10-114-00-001101](#) [383-10-127-00-001101](#) [383-10-126-00-001101](#) [383-10-125-00-001101](#) [383-10-124-00-001101](#) [383-10-123-00-001101](#) [383-10-122-00-001101](#) [483-10-208-00-001101](#) [483-10-206-00-001101](#) [483-10-204-00-001101](#) [483-10-220-00-001101](#) [483-10-218-00-001101](#) [483-10-216-00-001101](#) [483-10-214-00-001101](#) [483-10-212-00-001101](#) [483-10-210-00-001101](#) [399-10-106-10-009101](#) [399-10-107-10-009101](#) [399-10-116-10-009101](#) [399-10-102-10-009101](#) [399-10-105-10-009101](#) [399-10-113-10-009101](#) [399-10-112-10-009101](#) [399-10-111-10-009101](#) [399-10-110-10-009101](#) [399-10-109-10-009101](#) [399-10-108-10-009101](#) [399-10-115-10-009101](#) [399-10-117-10-009101](#) [399-10-103-10-009101](#) [399-10-114-10-009101](#) [399-10-118-10-009101](#) [399-10-130-10-009101](#) [399-10-124-10-009101](#) [399-10-123-10-009101](#) [399-10-122-10-009101](#) [399-10-121-10-009101](#) [399-10-120-10-009101](#) [399-10-119-10-009101](#) [399-10-131-10-009101](#) [399-10-129-10-009101](#) [399-10-127-10-009101](#) [399-10-126-10-009101](#)