



## SPECIFICATION

1. Rated Voltage .....9Vp-p Square Wave
2. Operating Voltage .....3~30Vp-p Square Wave
3. Max. Rated Current .....3mA/9Vp-p Square Wave/4KHz
4. Resonant Frequency .....4.0±0.5KHz
5. Min. Sound Pressure Level.....88dB/9Vp-p Square Wave/10cm
6. Capacitance at 100Hz.....12000pF±30%
7. Shell Material/Color .....PC/Black
8. Operating Temperature .....-20~+80°C
9. Store Temperature .....-30~+100°C
10. Weight .....1.2g

<b>Compliance with ROHS</b>			
<b>KEPO</b> NINGBO KEPO ELECTRONIC CO.,LTD <a href="http://www.chinaacoustic.com">http://www.chinaacoustic.com</a>			
<b>Piezo Buzzer</b>		<b>DAE YOUNG</b>	
<b>CBEG1740BP-1-1609</b>			
UNIT		DWG NO.	
mm		OEM1609R	
SCALE		SHEET	
		VER 1.0	

No.	DESCRIPTION	APPROVED	DATE
<small>           TOLERANCES UNLESS NOTED OTHERWISE:            .X *            .XX *            .XXX *            90° FORMED ±2°            ANGLES ±1°            FIRST ANGLE PROJECTION         </small>		APPROVALS	DATE
		DRAWN	DATE
		CHECKED	DATE
		APPROVED	06.05.09