



SECTION A-A

Material
Housing: PA66, UL94V-0
Clamp: Bronze, Ni Plated
Screws: M2 Steel, Zn plated
Shrapnel: Brass, Ni plated

Electrical
Rated voltage: 300V
Rated current: 8A
Contact Resistance: 20 mΩ
Insulation resistance: 500MΩ/DC500V
Withstand voltage: AC2000V / 1 min
Wire Range: 28 ~ 16AWG 1.0mm²

Mechanical
Temp. Range: -40 °C ~ +105 °C
Torque: 0.2Nm (1.7 bin)

Order Information

L-KLS2-EDK-3.96-XXP-4S00

RoHS

Terminal Block

Pitch

No.: of Pole

Color: 4- Green

Screw: S-Slot Screw C-Cross Screw

Product Code: 00 ~ 99

GENERAL TOLERANCE		ANGLE TOLERANCE		Description:
X. ±0.60	.X ±0.38	X. ±5°	.X ±3°	Plug-in TERM BLOCK 3.96MM
.XX ±0.25		.XX ±2°		
Draw by	2015-09-01	PROJECTION		KLS P/N: KLS2-EDK-3.96-XXP-4S-00
Check by	2015-09-15	UNITS	mm	NingBo KLS ELECTRONIC CO.,L TD.
SCALE		SHEET SIZE	A4	