

**6959 - ELBOW BODY POLYMER MALE BSPP SS
316L EPDM SEAL**



maximum working pressure 16 bar
2 MPa
232 psi

working temperature -10 to 130 °C
14 to 266 °F
263 to 403 °K

vacuum capability 755 mm Hg

body BIO-BASED
POLYMER

sub-base STAINLESS STEEL
316L

'O'-rings EPDM

gripping ring STAINLESS STEEL

Part Nb	ØD (MM)	C	E (mm)	F (mm)	ØG (mm)	H (mm)	L (mm)	(kg)
	All	All	All	All	All	All	All	All
6959 04 10	4	G1/8	4.5	13	8.5	22.5	19	.009
6959 04 13	4	G1/4	5.5	16	8.5	22.5	19	.014
6959 04 19	4	M5x0,8	3.5	10	8.5	23	19	.009
6959 06 10	6	G1/8	4.5	13	10.5	26.5	22.5	.011
6959 06 13	6	G1/4	5.5	16	10.5	26.5	22.5	.016
6959 06 19	6	M5x0,8	3.5	10	10.5	26.5	22.5	.008
6959 08 10	8	G1/8	4.5	13	13.5	35	29.5	.018
6959 08 13	8	G1/4	5.5	16	13.5	33	29.5	.02
6959 08 17	8	G3/8	5.5	21	13.5	33	29.5	.028
6959 10 13	10	G1/4	5.5	16	16	40.5	34	.029
6959 10 17	10	G3/8	5.5	21	16	39	34	.037
6959 10 21	10	G1/2	7	24	16	39	34	.042
6959 12 17	12	G3/8	5.5	21	19	42	40	.04
6959 12 21	12	G1/2	7	24	19	42	40	.049
6959 16 17	16	G3/8	7.5	27	27	54	52	.088
6959 16 21	16	G1/2	9	27	27	55	52	.084
6959 16 27	16	G3/4	10.5	32	27	55	52	.12