



3604 - EQUAL TEE MM



maximum working pressure	30 bar 3 MPa 435 psi
working temperature	-25 to 150 °C -13 to 302 °F 248 to 423 °K
vacuum capability	755 mm Hg
body	FDA CHEMICAL NICKEL PLATED BRASS
'O'-rings	FKM
collar	FDA CHEMICAL NICKEL PLATED BRASS
sealing washer	FDA CHEMICAL NICKEL PLATED BRASS

Part Nb	ØD (MM)	ØG (mm)	H (mm)	L_2 (mm)	(kg)
	All ▾	All ▾	All ▾	All ▾	All ▾
3604 04 00	4	10	23	18	.014
3604 06 00	6	12	28	21.5	.023
3604 08 00	8	15	31	23.5	.032
3604 10 00	10	17.5	37.5	29	.048
3604 12 00	12	19.5	40.5	31	.063
3604 14 00	14	21.5	45	34	.078