

Note: This datasheet may be out of date. Please download the latest datasheet of GRM2165C2A182JA01# from the official website of Murata Manufacturing Co., Ltd. http://www.murata com/en/products/productdetail?partno=GRM2165C2A182JA01%23

GRM2165C2A182JA01#

"#" indicates a package specification code.



< List of part numbers with package codes > GRM2165C2A182JA01J GRM2165C2A182JA01D

Appearance & Shape







Packaging	Specifications	Minimum Order Quantity
J	330mm Paper Tape	10000
D	180mm Paper Tape	4000

Mass (typ.)		
1 piece	6.4mg	
φ180mm Reel	126g	

1 of 4

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.





Note: This datasheet may be out of date. Please download the latest datasheet of GRM2165C2A182JA01# from the official website of Murata Manufacturing Co., Ltd. http://www.murata.com/en/products/productdetail?partno=GRM2165C2A182JA01%23

GRM2165C2A182JA01#

"#" indicates a package specification code.

Specifications

Length	2.0±0.1mm	
Width	1.25±0.1mm	
Thickness	0.6±0.1mm	
Capacitance	1800pF ±5%	
Distance between external terminals g	0.7mm min.	
External terminal size e	0.2 to 0.7mm	
Operating Temperature Range	-55°C to 125°C	
Rated Voltage	100Vdc	
Size code in inch(mm)	0805 (2012M)	
тс	0±30ppm/°C	
Temperature characteristics (complied standard)	C0G(EIA)	
Temperature range of temperature characteristics	25°C to 125°C	

2 of 4

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering. 2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.



Attention



Note: This datasheet may be out of date Please download the latest datasheet of GRM2165C2A182JA01# from the official website of Murata Manufacturing Co., Ltd. detail?partno=GRM2165C2A182JA01%23


Frequency CharacteristicR


GRM2165C2A182JA01#

"#" indicates a package specification code.

Characteristic Data

The charts below may show another part number which shares its characteristics.





AC Voltage[Vrms] GRM2165C2A182JA01 C-AC Voltage capchange, DCOV, 25.0d

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering




Attention




Note: This datasheet may be out of date. Please download the latest datasheet of GRM2165C2A182JA01# from the official website of Murata Manufacturing Co., Ltd. cts/productdetail?partno=GRM2165C2A182JA01%23

GRM2165C2A182JA01#

"#" indicates a package specification code.





Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering. 2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

4 of 4