

Crimping pliers - CRIMPFOX VARIO 4S - 1108766

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Crimping pliers, type of contact: Insulated and uninsulated ferrules, standards/specifications: DIN 46228-1, DIN 46228-4, min. cross section: 0.25 mm², max. cross section: 4 mm², compression: square, black/green

Your advantages

- Lateral conductor entry
- Proven high-quality technology
- "The original"
- Suitable for TWIN ferrules, thanks to continuous automatic adjustment
- Process reliability, thanks to pressure lock and self-adjusting die



Key Commercial Data

Packing unit	1 pc
GTIN	 4 063151 016029
GTIN	4063151016029

Technical data

Dimensions

Length (b)	190 mm
Width (a)	72 mm
Height (c)	22 mm

General

Note	DIN 46228-1, DIN 46228-4
Color	black/green
Compression	square
Type of contact	Insulated and uninsulated ferrules
Designation	Crimping position 1
Min. cross section	0.25 mm ²
Max. cross section	4 mm ²
AWG min	24
AWG max	12

Crimping pliers - CRIMPFOX VARIO 4S - 1108766

Technical data

General

Weight	401 g
Min. cross section	0.25 mm ²
Max. cross section	4 mm ²
AWG min	24
AWG max	12

Classifications

eCl@ss

eCl@ss 9.0	21043811
------------	----------

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		RU x- DE.xx08.B.02974
-----	---	--------------------------

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1108766](#)