

Section Links

A045 | A040 | A095 | A090 | A195 | A190 | A080 | A085 | A087 | A200 | A070 | A210 | A300 | **A315** | A089 | A125 | A105 | A205

Product Details

A315 Heavy Duty Low Profile Fixed Stud Levelling Foot - Stainless Steel Stud and Base with Inset Nitrile Rubber Pad

Materials Base - Stainless Steel Base with an Inset Nitrile Rubber Anti-Slip Pad
Stud - Stainless Steel



| Part No. | Thread Size D1 (mm) | Thread Length L (mm) | Base Diameter D2 (mm) | Overall Height H (mm) | Pad Thickness (mm) | Maximum Recommended Load (kg) |
|----------|------------------------|-------------------------|--------------------------|--------------------------|-----------------------|-------------------------------------|
| A315/001 | M12 | 75 | 60 | 90 | 3 | 1250 |
| A315/002 | M12 | 125 | 60 | 140 | 3 | 1250 |
| A315/003 | M12 | 150 | 60 | 165 | 3 | 1250 |
| A315/004 | M12 | 150 | 80 | 171 | 3 | 1500 |
| A315/005 | M16 | 150 | 80 | 171 | 3 | 2000 |
| A315/006 | M16 | 150 | 120 | 174 | 3 | 2000 |
| A315/007 | M20 | 200 | 120 | 224 | 3 | 3000 |
| A315/008 | M20 | 200 | 150 | 226 | 3 | 3000 |
| A315/009 | M24 | 200 | 150 | 226 | 3 | 4000 |

Dimensions are approximate

