

Starrett®

Starrett KFC06021RS Fast Cut Bi-Metal Holesaw Kit (604-731)



Features:

- 8 Pc Fast Cut Bi-Metal Holesaw Kit
- Holesaw Diameters: 16mm, 20mm, 25mm, 32mm, 40mm, 51mm
- Arbors: A1 (14-30mm), A10 (32mm-210mm)
- New tooth material with extra cobalt for enhanced heat and wear resistance - improving the product life
- New 5.5 TPI positive rake tooth form provides less torque for a smoother, faster cut in all materials
- 30% extra gullet volume for better material penetration
- Ideal for stainless steel and mild steel sheet, tubes and other materials with a thickness of up to 3mm (1/8 in)
- 41mm (1.5/8 in) hole saw depth
- Recommended cutting depth - up to 3mm (1/8 in)