

## Parallel male thread coupler

### Technical characteristics

**Profile:** European 10,4 mm

**Operating pressure:** 2 to 16 bar

**ID Passage:** 10,4 mm

**Construction:** Body : Stainless steel


**Technology:** "One push" safety system (avoids hose whip)

**Flow rate at 6 bar:** 3530 l/min ( $\Delta P = 0,6$  bar)

**Temperature:** -15°C to +70°C

**Highlight:** Anti-static, Excellent efficiency, Harsh conditions



	A (mm)	B (mm)	C (mm)	BSPP male thread	Parts Numbers
	100,4	37	26	G 3/8	ESI 111152
	101,4	37	26	G 1/2	ESI 111153
	105,9	37	32	G 3/4	ESI 111154