

RTP2C

Mono 2 pole



Article Variations

Article Name	Details	Packaging
RTP2C	nickel shell, nickel plated contacts	Plastic Packaging
RTP2C-D	nickel shell, nickel plated contacts	BULK
RTP2C-B	black shell, gold plated contacts	Plastic Packaging
RTP2C-B-D	black shell, gold plated contacts	BULK
RTP2C-BAG	black shell, nickel plated contacts	Plastic Packaging
RTP2C-BAG-D	black shell, nickel plated contacts	BULK

Technical Information

Product

Title	RTP2C
Connection Type	Plug

Electrical

Contact Resistance	≤10 mΩ
Insulation Resistance	>200 MΩ(Initial)
Dielectric Strength	500V dc 50HZ

Mechanical

Insertion and Withdrawal Force	≤60 N
Lifetime	>1,000 Mating Cycles
Cable O.D.	2 - 4 mm
Wiresize	0.24 mm ²
Wiresize	24 AWG

Material

Sleeve Assembly	Brass
Sleeve	Brass
Housing	Zinc
Sleeve Assembly	Nickel Plating
Sleeve	Nickel Plating
Housing	Nickel Plating