

39.10 | 39 - METRIC SHORT-REACH COMBINATION WRENCHES




Norm :


NF ISO 691, NF ISO 7738, NF ISO 3318, NF ISO 1711-1, E74-306, ISO 691, ISO 7738, ISO 3318, ISO 1711-1, DIN ISO 691, DIN 1711-1, ASME B107.100

Description :

- Short combination wrenches: the short handle and compact head allow for high handiness. Ideal for confined access. • OGV® profile with 12-point ring for powerful tightening while protecting the nut. H suffix = 6-point ring. • Ring head angled at 15°. • Open end head angled at 15°. • Metric sizes: 3.2 to 17 mm. • Presentation: satin chrome finish.



Informations :

	39.10
A [mm]	10
B x B1 [mm]	21,5 x 15,3
E [mm]	5,1
E1 [mm]	6,4
L [mm]	103
Hex Size - 12-point [mm]	12
[kg]	0.030