

113A.15T | 113A.T - PHOSPHATED ADJUSTABLE WRENCHES




Norm :


NF ISO 6787, ISO 6787, DIN 3117, ASME B107.100


Description :

- Good access to the button = easy setting.
- Non-protruding moving jaw at maximum capacity.
- Pre-adjustment of jaw opening thanks to millimetric gradation.
- Left-hand button rotation.
- Range from 4" to 24".
- Presentation: phosphated body and "fine ground" head faces.



Informations :

	113A.15T
A [mm]	44
B [mm]	97
C x C1 [mm]	28,0 x 35,0
E [mm]	13,5
E1 [mm]	20,0
E2 [mm]	12,0
E3 [mm]	14,8
E4 [mm]	11,5

	113A.15T
L [mm]	380
L1 [mm]	44
[kg]	1.200