

## FEATURES

- 4, 5 and 8-way Variants
- Insulation Resistance  $\geq 100 \text{ M}\Omega$
- Neoprene O-Ring
- Brass nickel plated coupling nut

# RS PRO M12 FEMALE STRAIGHT USER-WIRE 5 PIN PG9 WITH PLASTIC BODY SCREW TERMINALS

RS Stock No.: 2080560



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

### ATTRIBUTE 1

## M12 female cable connector

The re-wireable circular connectors have a threaded mating mechanism with A coding, preventing incorrect mating. Along with IP67 ingress rating. These connectors are best suited to environments that demand a more rugged connector solution.

### Features and Benefits:

- 4, 5 and 8-way Variants
- Insulation Resistance  $\geq 100 \text{ M}\Omega$
- Neoprene O-Ring
- Re-Wireable –no special tooling required
- Brass nickel plated coupling nut

### General Specifications

|                           |                            |
|---------------------------|----------------------------|
| Rated Operational Voltage | 60 V                       |
| Current Rating            | 4A                         |
| Insulation Resistance     | $\geq 100 \text{ M}\Omega$ |
| Temperature Range         | -25°C ... +75°C            |
| Coding                    | A-Coded                    |

### Material Specifications

|                 |                     |
|-----------------|---------------------|
| Grip Material   | Nylon 66            |
| Contact         | Cu-Zn               |
| Contact Plating | Gold Flash          |
| Contact Carrier | Nylon 66            |
| O-Ring          | Neoprene + NBR      |
| Grip Color      | Black               |
| Termination     | Screw               |
| Pole            | 5                   |
| Cable Gland     | 6 - 8 mm (PG9)      |
| Coupling Nut    | Brass Nickel-Plated |

### Protection Category

|                      |      |
|----------------------|------|
| Degree of Protection | IP67 |
|----------------------|------|

## Additional Information

**Custom Tariff Number** 85369090


## Approvals

**Standards Met** IEC 61076-2-101

## Similar Products

| Stock No. | Brand  | Product Name                                  | Attribute 1                            | Attribute 2           |
|-----------|--------|---|--|-----------------------|
| 877-1101  | RS PRO | RS Pro User Wire Connector 5 Pin Straight PG7 | Industrial Automation Cable Assemblies | Actuator/Sensor Cable |
| 877-1107  | RS PRO | RS Pro User Wire Connector Angled 5 Pin PG7   | Industrial Automation Cable Assemblies | Actuator/Sensor Cable |

## Connection Diagrams / Assembly Diagrams / Illustrations / Accessories



All Dimensions are in mm.