

# D-SUB HIGH DENSITY

Solder pin – Angled – .350" / 7.98 mm – Stamped contacts – Plastic bracket




RoHS compliant – CSA listed, File No.: LR 115000-1 – UL listed, File No.: E202784

## DESCRIPTION


- Mounting styles:
  - with mounting bracket, PCB clip and 4-40 UNC hex nut
  - with mounting bracket, PCB clip and 4-40 UNC threaded insert
- Quality class 3 (other quality classes on request)
- Shell: Steel tin plated

## SOCKET CONNECTOR




No. of pos.	A -0.76	B +0.25	C
15	31.19	16.46	25.00 +0.12
26	39.52	24.79	33.30 +0.15 -0.10
44	53.42	38.50	47.04 +0.13
62	69.70	54.96	63.50 +0.13
78	67.31	52.55	61.10 +0.14 -0.11



## PLUG CONNECTOR




No. of pos.	A -0.76	B +0.25	C	D -0.3
15	31.19	16.79	25.00 +0.12	6.12
26	39.52	25.12	33.30 +0.15 -0.10	6.12
44	53.42	38.84	47.04 +0.13	5.99
62	69.70	55.30	63.50 +0.13	5.99
78	67.31	52.68	61.10 -0.14 0.11	5.99




15-62 pos.




15-62 pos.



78 pos.



78 pos.



## ORDER DATA

SOCKET CONNECTOR		
No. of pos.	Mounting style 4-40 UNC	Part Number
15	PCB clip / Hex bolt	302 A 10869 X
26	PCB clip / Hex bolt	302 A 10879 X
44	PCB clip / Hex bolt	302 A 10889 X
62	PCB clip / Hex bolt	302 A 10899 X
78	PCB clip / Hex bolt	302 A 11629 X

PLUG CONNECTOR		
No. of pos.	Mounting style 4-40 UNC	Part Number
15	PCB clip / Hex bolt	301 A 10869 X
26	PCB clip / Hex bolt	301 A 10879 X
44	PCB clip / Hex bolt	301 A 10889 X
62	PCB clip / Hex bolt	301 A 10899 X
78	PCB clip / Hex bolt	301 A 11369 X

SOCKET CONNECTOR		
No. of pos.	Mounting style 4-40 UNC	Part Number
15	PCB clip / Threaded insert	DLH 1XS 8 AK53 X
26	PCB clip / Threaded insert	DLH 2XS 8 AK53 X
44	PCB clip / Threaded insert	DLH 3XS 8 AK53 X
62	PCB clip / Threaded insert	DLH 4XS 8 AK53 X
78	PCB clip / Threaded insert	DLH 5XS 8 AK53 X

PLUG CONNECTOR		
No. of pos.	Mounting style 4-40 UNC	Part Number
15	PCB clip / Threaded insert	DLH 1XP 8 AK53 X
26	PCB clip / Threaded insert	DLH 2XP 8 AK53 X
44	PCB clip / Threaded insert	DLH 3XP 8 AK53 X
62	PCB clip / Threaded insert	DLH 4XP 8 AK53 X
78	PCB clip / Threaded insert	DLH 5XP 8 AK53 X

PCB clip .122" / 3.1 ± .004" / 0.10 mm hole diameter and .063" / 1.6 mm circuit board thickness

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[DLH1XS8AK53X](#) [301A10899X](#) [DLH1XP8AK53X](#) [DLH2XP8AK53X](#) [DLH2XS8AK53X](#)