



**Notes:**

1. Electrical Specifications:
  - Meets EIA/TIA-568-B.2 Cat.5e Specification
  - Contact Resistance: 20mOhm max.
  - Insulation Resistance: 500MOhm min. @ 100 VDC
  - Current Rating: 1.2A max. at 25° C
  - Working Voltage: 100 VDC
  - DWV: 1000 VDC/60s Contact to Contact, 1500 VDC/60s Contact to Metal Shell
  - Operating Temperature: -40° C to +85° C
2. Material and Finish:
  - Coupling Ring and Plug Housing: Polyester (Black) or Metallized ABS, UL94 V-0 (Nickel Plated) or Zinc Die-cast (Nickel Plated) ;
  - Interfacial Seal: Silicone, Color: White
  - Cable Fitting: PA (Black), UL94 V-0 or Brass, Nickel Plated
  - Cable Fitting Rubber Ring: NBR, Color: Black
  - RJ45 Plug Metal Shell: Copper Alloy, Nickel Plated
  - ⑨ - RJ45 Plug Plastic Housing: Clear Polycarbonate UL94 V-2
  - RJ45 Plug Contacts: Phosphor Bronze, Finish: 50u" Gold min. over Nickel
3. RJ45 Plug accepts both Stranded and Solid Cables with Outer Diameter of 4.83mm to 6.73mm
4. Plastic Version Cable Fitting accepts Cable Outer Diameter Range of 4mm to 8mm
5. Metal Version Cable Gland accepts Cable Outer Diameter Range of 4.5mm to 8mm
- ⑥ 6. IP67 rated when fully mated with the appropriate mating connector

Directive 2002/95/EC RoHS Compliant

Version	Part Number
Plastic Version	17-10001
Metallized Plastic Version	17-10013
Zinc Die-cast Version	17-10044

Customer:			Tolerance Unless otherwise specified		Scale: 1.5:1	Dim. in mm	
			0 PLC ±0.50	1 PLC ±0.38			
Name			Approval Date		Autodesk Inventor	Material: See Notes	
h	2 x h	Jun/25/2014	Vincent ke	2006			Date
g	1 x g	Jul/06/2011	Vincent Ke	Draw.	Oct. 24	Vincent Ke	
f	1 x f	Nov/26/2009	Vincent Ke	Appd.	Oct. 24	J. Chaudry	
e	1 x e	May/25/2009	Vincent Ke	Norm			
d		Jun/18/2007	Vincent ke	D-old			
c		May/15/2007	Vincent ke				
a	original						
Rev.	Changes	Date	Name				DIN A3
Title: RJ45 Plug Kit Industrial Ethernet Connector (IP67) with shielded Cat. 5e RJ45 Plug							Sheet 1/1
Drawing No.: 39K1A204							
Part No.: SEE P/N ABOVE							

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY MANNER AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC CORPORATION.

DOT NOT ALTER CAD DRAWING BY HAND

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CONEC:](#)

[17-10044](#) [17-10013](#) [17-10001](#)