


TECHNICAL SPECIFICATIONS SN-Series

Material: UL-Recognized Plastic
Operating Temperature: -30°C to +90°C
Cable Entry: Top
Thumbscrews: UNC 4-40
Cable Diameter: Up to 11,5 mm



- Available with Short Jack Screws only
- Available in 9, 15 & 25 Way options
- Available in two colours - Black or Light Grey
- Manufactured in UL94HB material
- Custom Colours available


Order Code

Series: _____	MHCCOV	XX	SN	BK
Size (xx): 9,15, 25 _____				
Type: _____				
SN = Snap Together Hood				
Colour: _____				
BK = Black, LG = Light Grey				

Size	Dim A	Dim B
9-way	30,5	39,2
15-way	40,1	39,6
25-way	53,6	42,1

TECHNICAL SPECIFICATIONS SC-Series

Material: UL-Recognized Plastic
Operating Temperature: -30°C to +90°C
Cable Entry: Top
Thumbscrews: UNC 4-40
Cable Diameter: Up to 11,5 mm



- Available with Short or Long Jack Screws
- Available in 9, 15, 25, 37 & 50 Way options
- Available in two colours - Black or Light Grey
- Manufactured in UL94HB material
- Custom Colours available

Order Code

Series: _____	MHCCOV	XX	SCL	BK
Size (xx): 9,15, 25, 37, 50 _____				
Type: _____				
SC = Short Jackscrew SCL = Long Jackscrew				
Colour: _____				
BK = Black, LG = Light Grey				

Size	Dim A	Dim B
9-way	31,4	40,2
15-way	39,6	35,8
25-way	55,0	42,0
37-way	69,0	51,0
50-way	69,5	43,9