

PRODUCT-DETAILS

AL28/M25/A/BL

M25 NC28 ADAPTALOK BLK STR



General Information

Extended Product Type	AL28/M25/A/BL
Product ID	7TCA296000R0797
EAN	5020963000713
Catalog Description	M25 NC28 ADAPTALOK BLK STR
Long Description	Straight Conduit Fitting, Fixed External Male Thread, Nominal Conduit Size 28mm, M25 Thread, Polyamide (Nylon) 66, Black

Ordering

EAN	5020963000713
Customs Tariff Number	3917400090

Dimensions

Product Net Weight	.038 lb 17.234 g
--------------------	---------------------

Container Information

Package Level 1 Units	10 piece
Package Level 1 Width	6 in 152 mm
Package Level 1 Height	6 in

	152 mm
Package Level 1 Depth / Length	2 in 51 mm
Package Level 2 Units	150 piece
Package Level 2 Width	14 in 356 mm
Package Level 2 Height	14 in 356 mm
Package Level 2 Depth / Length	6 in 152 mm

Additional Information

Application	For Insertion into Threaded Entries or Knockout to Connect Conduit
Brand / Label	Adaptaflex
Cable Entry Position	M25 Thread
Color	Black
Material	Polyamide/Nylon 6.6
Number of Batteries	0
Product Name	plastic fitting for conduit
Product Type	Conduit Fitting with Metric Threads
Size	NC 28mm
UPC	786210280165

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	AL28/M25/A/BL
Declaration of Conformity - CE	9AKK107492A9618
Instructions and Manuals	AL28/M25/A/BL

Classifications

ETIM 6	EC001176 - Screw connection for corrugated plastic hose
ETIM 7	EC001176 - Screw connection for corrugated plastic hose
UNSPSC	39121311
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	4441 >> Electrical fittings

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

