

Dura-Ty™ Cable Ties

Dura-Ty™ Cable Ties are used to secure and route cables in outdoor power and communication applications. The acetal material provides excellent ultraviolet resistance, strength, and durability for a long service life. The tie design includes double stainless steel locking barbs to ensure consistent and reliable cable tie operation. Dura-Ty™ Cable Ties are available in two cross sections, a range of discrete lengths, and cut-to-size rolls for application flexibility. The new Heavy cross section features a robust head design that allows the tie to be tightened over a wide range of angles for a safe and reliable installation, and it incorporates a textured strap surface that improves gripping ability. The Extra-Heavy cross section meets Telcordia TR-TSY-000789 guidelines for lashed cable supports. Dura-Ty™ Cable Ties along with Panduit cable tie installation tools and stackable aerial cable spacers are the ideal solution for outdoor bundling applications.



Key Features	Benefits
Acetal material	Provides twenty plus years weatherability life for tough outdoor applications; high impact resistance, and strength
Double stainless steel locking barbs	Offer a durable locking mechanism for consistent cable tie operation; high tensile strength
Robust head design*	Allows tie to be tightened over a wide range of angles for application flexibility
Textured strap surface*	Improved grip makes it easier to handle and install the cable tie
Flexible strap body*	Permits cable tie to easily conform to irregular bundle shapes while maintaining loop tensile strength; easy to use
Convenient reel dispenser pack	Allows installer to cut-to-size for customized field applications; part number reduction contributes to reduced inventory costs
Discrete length cable ties**	Offers several pre-cut sizes for fast installation

*Heavy cross section only.
 **Extra-Heavy cross section only.



Heavy Cross Section –
 Textured strap body and robust head design for reliable installations



Dura-Ty™ Kit –
 Recyclable dispenser pack has through-hole for attaching to belt plus storage area for bag of heads



Stackable Aerial Cable Spacer –
 Designed for use in parallel or perpendicular applications with Dura-Ty™ Cable Ties

Ordering Information

Strapping, Heads, and Kit – Allows User to Customize Length

Standard Part Number	Description	Strap Length Ft. (m)	Strap Width In. (mm)	Strap Thickness In. (mm)	Min. Loop Tensile Strength Lbs. (N)	Head Height In. (mm)	Head Width In. (mm)	Recommended Tools	Pkg.* Qty.
----------------------	-------------	----------------------	----------------------	--------------------------	-------------------------------------	----------------------	---------------------	-------------------	------------

Heavy Cross Section

DTRH-LR0	Cable tie strapping (reel)	50.0 (15)	0.331 (8.40)	0.064 (1.63)	200 (890)	—	—	GTH-E, GS4EH, ST3EH, STHV, STH2	1
DTHH-Q0	Cable tie heads (bag of 25)	—	—	—	—	0.393 (9.98)	0.557 (14.15)	—	25
DTKH-0	Kit containing 50' reel of strapping and 25 cable tie heads	50.0 (15)	0.331 (8.40)	0.064 (1.63)	200 (890)	0.393 (9.98)	0.557 (14.15)	GTH-E, GS4EH, ST3EH, STHV, STH2	1

Extra-Heavy Cross Section

DTREH-LR0	Cable tie strapping (reel)	50.0 (15)	0.500 (12.70)	0.059 (1.50)	250 (1112)	—	—	GS4EH, ST3EH	1
DTHEH-Q0	Cable tie heads (bag of 25)	—	—	—	—	0.490 (12.45)	0.718 (18.24)	—	25
DTKEH-0	Kit containing 50' reel of strapping and 25 cable tie heads	50.0 (15)	0.500 (12.70)	0.059 (1.50)	250 (1112)	0.490 (12.45)	0.718 (18.24)	GS4EH, ST3EH	1

Discrete Lengths – Pre-Cut Sizes

Standard Part Number	Length In. (mm)	Width In. (mm)	Thickness In. (mm)	Head Height In. (mm)	Head Width In. (mm)	Max. Bundle Diameter In. (mm)	Min. Loop Tensile Strength Lbs. (N)	Recommended Tools	Pkg.* Qty.
----------------------	-----------------	----------------	--------------------	----------------------	---------------------	-------------------------------	-------------------------------------	-------------------	------------

Extra-Heavy Cross Section

DT4EH-L0	13.5 (343)	0.495 (12.57)	0.059 (1.50)	0.490 (12.45)	0.718 (18.24)	3.8 (98)	250 (1112)	GS4EH, ST3EH	50
DT8EH-Q0	27.0 (686)					8.0 (203)			25
DT14EH-L0	48.0 (1219)					14.0 (355)			50
DT15EH-L0	53.0 (1346)					15.0 (381)			50
DT28EH-C0	96.0 (2438)					28.0 (711)			100
DT44EH-C0	144.0 (3658)					44.0 (1117)			100

Stackable Aerial Cable Spacer – Weather Resistant Polypropylene



- Each spacer snaps into another to increase spacer heights by 1/2" increments
- Designed for use in parallel or perpendicular applications

Standard Part Number	Used with Cable Ties	Length In. (mm)	Width In. (mm)	Height In. (mm)	Pkg.* Qty.
SACS50-T100	All Dura-Ty™ Cable Ties	2.08 (52.8)	1.16 (29.5)	0.71 (18.0)	200

Cable Tie Installation Tools

Part Number	Used With Cable Ties	Weight oz. (g)	Part Description	Pkg.* Qty.
GTH-E	DTRH, DTKH	11.9 (337)	Tool controlled tension and cut-off. Ergonomic design.	1
STHV		12.0 (341)	Installer controlled tension and cut-off. Steel construction.	1
STH2		2.5 (71)	Installer controlled tension and cut-off. Plastic construction.	1
GS4EH	DTRH, DTKH, DT4EH, DT8EH, DT14EH, DT15EH, DT28EH, DT44EH, DTREH, DTKEH	16.0 (454)	Tool controlled tension and cut-off.	1
ST3EH		9.0 (256)	Installer controlled tension and cut-off. Steel construction.	1

*Order the number of pieces required, in multiples of standard package quantity.

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT CANADA
Markham, Ontario
cs-cdn@panduit.com
Phone: 800.777.3300

PANDUIT EUROPE LTD.
London, UK
cs-emea@panduit.com
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.
Republic of Singapore
cs-ap@panduit.com
Phone: 65.6379.6700

PANDUIT JAPAN
Tokyo, Japan
cs-japan@panduit.com
Phone: 81.3.3767.7011

PANDUIT LATIN AMERICA
Jalisco, Mexico
cs-la@panduit.com
Phone: 52.333.666.2501

PANDUIT AUSTRALIA PTY. LTD.
Victoria, Australia
cs-aus@panduit.com
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

For more information

Visit us at www.panduit.com

Contact Customer Service by email: cs@panduit.com
or by phone: 800-777-3300

PANDUIT®

©2016 Panduit Corp.
ALL RIGHTS RESERVED.
CTCB61--WW-ENG
replaces WW-CTCB40
3/2016

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[DTHEH-Q0](#) [DT8EH-Q0](#) [DTKEH-0](#) [DTHH-Q0](#) [DTRH-LR0](#) [DT44EH-C0](#) [DT14EH-L0](#) [DT28EH-C0](#)