

PRODUCT SPECIFICATION

**Carl
Kammerling**
International

Brand	C.K
Product Range	RedLine pliers
Catalogue number	3750, 3751, 3720, 3967, 3803, 3804, 3906, 3907, 3909 & 3754
Date	18/02/2009

Range Description

A range of professional quality pliers and cutters

Features

- Hot drop forged from special alloy steel for strength and durability
- Ergonomically designed sleeves for comfort and effortless use
- Contoured anti slip shoulders for safety in use
- Dual compound technology features soft grip non-slip inlays for grip and control
- Matt chrome finish for corrosion protection
- Gas/Oil hardened for optimum performance
- Induction hardened and precision ground cutting edges for precision cutting and long life



3751



3750



3720



3967



3803/4



3909



3906



3907



3754



3964

Item Number	Item Description	EAN No	Commodity code	Carton Qty
T3751 5	C.K RedLine Side cutters 130mm	5013969496901	82032090	3
T3751 55	C.K RedLine Side cutters 145mm	5013969497007	82032090	3
T3751 6	C.K RedLine Side cutters 160mm	5013969497106	82032090	3
T3751 7	C.K RedLine Side cutters 180mm	5013969497205	82032090	3
T3750 145	C.K RedLine Side cutters 145mm	5013969141900	82032090	3
T3750 160	C.K RedLine Side Cutters 160mm	5013969142006	82032090	3

T3750 180	C.K RedLine Side Cutters 180mm	5013969974584	82032090	3
T3720 65	C.K RedLine High Leverage Side Cutters 165mm	5013969493900	82032090	3
T3720 8	C.K RedLine High Leverage Side Cutters 200mm	5013969494006	82032090	3
T3867 6	C.K RedLine Combination Pliers 160mm	5013969508901	82032090	3
T3867 7	C.K RedLine Combination Pliers 180mm	5013969509007	82032090	3
T3867 8	C.K RedLine Combination Pliers 200mm	5013969509106	82032090	3
T3803	C.K RedLine Pliers Set Containing 3867 180mm Combination Pliers, 3750 160mm Side cutters & 3906 200mm Snipe Nose Pliers	5013969774900	82032090	1
T3804	C.K RedLine Pliers Set Containing 3754 160mm Wire Stripping Pliers, 3750 160mm Side cutters & 3906 200mm Snipe Nose Pliers	5013969979831	82032090	1
T3909 5	C.K RedLine Snipe Nose Pliers 145mm	5013969511109	82032090	3
T3909 6	C.K RedLine Snipe Nose Pliers 170mm	5013969511208	82032090	3
T3906 8	C.K RedLine Snipe Nose Pliers 200mm	5013969510805	82032090	3
T3907 8	C.K Redline Bent Snipe Nose Pliers (45 deg) 200mm	5013969510904	82032090	3
T3964 6	C.K Redline Cable Cutters 160mm	5013969986709	82032090	3
T3754	C.K Redline Wire Stripping Pliers 160mm	5013969497502	82032090	3

Technical product information	Cutting capacities				
			Cutting Capacity mm diameter wire		
			Hard 2200MPa	Med/Hard 1600MPa	Soft 220MPa
	Item No	Description			
	T3751 5	C.K RedLine Side cutters 130mm	1.2	1.6	>4.0
	T3751 55	C.K RedLine Side cutters 145mm	1.4	1.9	>4.0
	T3751 6	C.K RedLine Side cutters 160mm	1.6	2.1	>4.0
	T3751 7	C.K RedLine Side cutters 180mm	1.8	2.3	>4.0
	T3750 145	C.K RedLine Side cutters 145mm	1.4	1.9	>4.0
	T3750 160	C.K RedLine Side Cutters 160mm	1.6	2.1	>4.0
	T3750 180	C.K RedLine Side Cutters 180mm	1.8	2.3	>4.0
	T3720 65	C.K RedLine High Leverage Side Cutters 165mm	2.0	2.5	>4.0
T3720 8	C.K RedLine High Leverage Side Cutters 200mm	2.5	3.0	>4.0	
T3867 6	C.K RedLine Combination Pliers 160mm	1.6	2.5	>4.0	
T3867 7	C.K RedLine Combination Pliers 180mm	1.6	2.5	>4.0	
T3867 8	C.K RedLine Combination Pliers 200mm	2.0	2.8	>4.0	
T3909 5	C.K RedLine Snipe Nose Pliers 145mm	1.6	2.0	>4.0	
T3909 6	C.K RedLine Snipe Nose Pliers 170mm	1.6	2.0	>4.0	
T3906 8	C.K RedLine Snipe Nose Pliers 200mm	1.6	2.0	>4.0	
T3907 8	C.K Redline Bent Snipe Nose Pliers (45 deg) 200mm	1.6	2.0	>4.0	
T3964	C.K Redline Cable Cutter 160mm	-	-	>16.0	
The T3754 Wire stripping pliers will strip wires from 0.3 to 5mm diameter					

Standards compliance	Side cutters - DIN ISO 5749 Combination Pliers - DIN ISO 5746 Snipe Nose Pliers - DIN ISO 5745 Wire Stripping Pliers - DIN ISO 5232
User health and safety information	None applicable
RoHS/WEEE compliance	These products do not fall within the scope of RoHS or WEEE regulations
Material safety data	None applicable
Warranty	C.K tools are guaranteed for life against imperfect materials or workmanship Normal wear and tear or damage caused through inappropriate use is not covered
Country of origin	Germany

Dimensional details

Item	Product only				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
T3751 5	56	25	140	116	56	30	235	130
T3751 55	55	25	150	144	55	30	230	158
T3751 6	60	25	170	199	60	30	260	213
T3751 7	60	25	190	260	60	30	290	274
T3750 145	60	25	155	157	60	30	230	171
T3750 160	55	25	165	182	55	30	240	196
T3750 180	65	25	190	236	65	30	260	250
T3720 65	57	25	180	233	57	30	240	247
T3720 8	55	25	210	297	55	30	255	311
T3867 6	70	25	170	199	70	30	260	213
T3867 7	65	25	180	217	65	30	250	231
T3867 8	60	25	207	297	60	30	260	311
T3803					190	40	250	720
T3804					190	40	250	665
T3909 5	55	25	150	118	55	30	220	132
T3909 6	55	25	180	166	55	30	230	180
T3906 8	60	25	205	198	60	30	240	212
T3907 8	60	25	210	196	60	30	245	210
T3964 6	70	25	170	199	70	30	255	213
T3754	55	25	170	171	55	30	240	185

Item	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
T3751 5	80	250	65	459		
T3751 55	80	250	65	543		
T3751 6	90	290	60	727		
T3751 7	90	290	60	909		
T3750 145	80	250	65	582		
T3750 160	80	250	65	669		
T3750 180	90	290	60	819		
T3720 65	80	250	65	810		
T3720 8	90	290	60	1021		
T3867 6	90	290	60	729		
T3867 7	80	250	65	762		
T3867 8	90	290	60	1020		
T3803						
T3804						
T3909 5	80	250	65	467		
T3909 6	80	250	65	611		
T3906 8	80	250	65	705		
T3907 8	90	290	60	717		
T3964 6	80	250	70	708		
T3754	80	250	65	625		

Packaging waste details

Item	Primary Packaging				Secondary packaging			
	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
T3751 5	14	Hanger					69	Box
T3751 55	14	Hanger					69	Box
T3751 6	14	Hanger					87	Box
T3751 7	14	Hanger					87	Box
T3750 145	14	Hanger					69	Box
T3750 160	14	Hanger					87	Box
T3750 180	14	Hanger					69	Box
T3720 65	14	Hanger					69	Box

T3720 8	14	Hanger					87	Box
T3867 6	14	Hanger					87	Box
T3867 7	14	Hanger					69	Box
T3867 8	14	Hanger					87	Box
T3803			102	Box				
T3804			102	Box				
T3909 5	14	Hanger					69	Box
T3909 6	14	Hanger					69	Box
T3906 8	14	Hanger					69	Box
T3907 8	14	Hanger					87	Box
T3964 6	14	Hanger					69	Box
T3754	14	Hanger					69	Box