

314DI Audio Stix™

NEW PRODUCT BULLETIN 623

AudioStix™....adding to the line

An addition has been added to the popular AudioStix™ line of premium pro audio products. The 314DI is a pocket size version of Switchcraft's standard high quality DI Box series of products.

Converts the unbalanced outputs of guitars, keyboards and other instruments with line-out level to balanced, mic level signals that can be connected to audio consoles and mic pre-amps.

FEATURES & BENEFITS

- 1/4" Feed Thru – allows for connection to multiple devices such as an amp and a tuner; two amps and much more.
- Switchcraft DE Series Locking Male XLR provides balanced, mono, mic level output
- Ground Lift Switch
- -20db pad to enable the device to handle stronger signals without distortion




Switchcraft®

314DI Active Instrument Direct Box Audio Specifications

Switchcraft®

Parameter	Performance	Conditions
Frequency Response	15Hz - 40kHz	+/-0.3dB, ref 1kHz
Total Harmonic Distortion + Noise	< 0.009%	at 1kHz, +4dBu Input, 22kHz Bandwidth
Maximum Input Level	+12.5dBu +23dBu	at 20Hz with 1% THD+Noise With 20dB Pad Engaged
Input Impedance	> 120kΩ	at 1kHz
Output Impedance	< 45Ω	at 1kHz
Deviation from Linear Phase	≤ 1°	at 1kHz
Voltage Gain	-22dB -42dB	+/-1dB +/-1dB with 20dB pad engaged
Pad Attenuation	20dB	+/-1dB



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[314DI](#)