



Datasheet

RS PRO Straight Plug Male 2 pin Solder Brass OD 5.2-6.2mm

Stock No: 209-5669



RS Pro's range of Chrome plated Brass push-pull locking connectors offer exceptional quality that is found in many cutting-edge connectors, including full 360° EMC shielding and high mating life. As has become standard within the RS Pro brand you can expect high quality products but at a reasonable price. These connectors are ideal for use in medical devices, testing equipment, audio equipment and other high-end indoor applications.

Features & Benefits:

- Push-pull latching system
- Chrome plated Brass
- IP50
- 360° Screening for full EMC shielding
- 15A Current Rating

Technical

| Characteristics | Value Standard | | |
|---------------------------|-----------------------------------|----------------------|--|
| Endurance | >5000cycles | IEC60512-5test9a | |
| Humidity | Up to 95% at 60°C | | |
| Temperature range | -55°C, +250°C | | |
| Resistance to vibration | 10-2000Hz,15g IEC 60512-4 test 6d | | |
| Shock resistance | 100g, 6ms IEC 60512-4 test 6c | | |
| Salt spray corrosion test | >96hrs | IEC 60512-6 test 11f | |
| Protection index (mated) | IP50 | IEC 60529 | |
| Climatical category | 55/175/21 | IEC 60068-1 | |


Electrical

| Characteristics | | Value | Standard |
|-----------------|----------|--------|---------------|
| Shielding | at 10MHZ | >75 dB | IEC 60619-1-3 |
| efficiency | at 1GHZ | >40 dB | IEC 60619-1-3 |





Dimensional line drawings



CONNECTOR SOLDER CUP VIEW























2(\$1.3)

 $3(\phi 1.3)$

4(\$0.9)

5 (\$0.9)

7(\$0.7)

8(\$0.7)

10 (\$0.5)

16 (#0.5)

Quality Standards







