



3 JAHRE
 YEARS
 GARANTIE
 WARRANTY

ANSMANN Future T350FR

- High-quality rechargeable aluminium torch for professional use
- Uses 5W CREE high-performance LED
- Seamless focussing by sliding the lamp head - from a precise point of light to homogeneous floodlighting
- On/off button and non-slip exterior for maximum user comfort, ideal for single-handed use
- Battery charge status indicator integrated into the button
- Integrated USB plug for direct charging with standard USB port
- Four light functions: 100% / 20% lighting power, strobe and dimming functions
- Brightness: 300 lumen (100%), 60 lumen (20%)
- Battery life ca. 2 h (100%), ca. 5.5 h (30%)
- Light range: Up to 110 m
- Protection: IP54
- Includes lithium-ion rechargeable battery pack 3.7V/700mAh (with integrated safety electronics) and wrist strap

INFORMATION

Product name	Future T350FR
Part No.	1600-0247
EAN-Code	4013674147939
Customs tariff number	8513100000
Material Group	02
Product content	T350FR torch, wrist strap, operating instructions

Product	94 × 27 × 27 mm / 93g
Packing + Product	125 × 34 × 272 mm / 150g
Packing Unit	6 (240 × 135 × 285 mm)

