


# Digital RGBD IP20 Flexible Tape



- Dynamic colour chasing modes
- Cascading connectors
- High quality UV stable polyurethane coating enables non discolouration and is scratch resistant for longer life
- High grade thick 3M adhesive backing for easy installation
- 50,000 hours working life
- Multiple applications for commercial and residential environments
- Precise LED binning section enables 100% consistent colour temperature from batch to batch



## Specification

Part Code	<b>F10-RGBD-12-48</b>
Voltage	12VDC
Power Consumption	11.2W
LED Qty	48 per mtr
Addressing Range	3 LEDs Addressable
Maximum Cascading Length	50M
Colour	RGB
IP	IP20
IP Finish	Glue filled silicon tube
Back Adhesive	VHB 3M adhesive tape
Working Temperature	-30°C ~ +70°C
Dimensions	5000 x 15.4 x 6.3mm


## FUNCTIONS

Dynamic Mode	99
Dynamic Speed Levels	10
Static Colour	29 Colours
Static Colour Brightness	10 Levels

## POWER & LED CONNECTORS

Power Connector	5.5mm DC female jack 10
Strip Connector	4-Pin SM type connector on both ends

## Mechanical Diagrams



This digital LED Strip can be made to any length up to 5 meters as a special order.

