

DIGITUS HDMI® AOC Hybrid Fiber Optic Cable, UHD 4K, 30 m

AK-330125-300-S
EAN 4016032462064



HDMI AOC hybrid-fiber connection cable, Type A M/M, 30m, UHD 4K@60Hz, CE, gold, bl

This active HDMI® AOC hybrid fiber optic cable is ideally suited for transferring uncompressed video and audio data with high bandwidth over longer distances. The hybrid construction, which uses copper and fiber optic cable, prevents electromagnetic interference. This ensures a loss-free transfer along the entire length of the cable with UHD resolution of up to 4K/60Hz and bandwidths of up to 18 Gbps. The use of fiber optic cable keeps the diameter of this active cable very low and gives it a very tight bending radius and low weight. It is ideal for use in homes, meeting rooms, and conference rooms as well as within buildings — and these are just a few of the possible uses. The simple Plug and Play installation is user-friendly; just plug it in and immediately enjoy optimal image quality. It supports numerous standards such as HDMI 2.0b, HDCP 2.2, and HDR. As far as audio goes, features such as ARC, DTS-HD Master Audio, Dolby TrueHD and many more are supported. Cutting edge chip technology makes it possible to transfer the full HDMI® signal spectrum while also supporting uncompressed CED and EDID with very low latency.

Transfer of uncompressed video and audio signals over a distance of up to 30 m in UHD 4K resolution with 18 Gbps bandwidth.

- Supports up to 4K with 50/60Hz
- Supports up to 4K 3D
- Data transfer rate of up to 18Gbps
- Supports up to 120Hz at Full HD
- Supports 1080p 3D HFR
- Supports YUV 4:4:4

- HDCP 2.2, HDCP 1.4
- HDMI 2.0b (backwards-compatible)
- Supports Deep Color (30-bit colour depth)
- Supports HDR (High Dynamic Range)
- Supports audio return channel (ARC)
- Supports Consumer Electronic Control (CEC)
- Supports Lip Sync (Audio/Video synchronisation)
- With Ethernet channel (HEC)
- Multi Stream audio/video support
- Supports 21:9 Cinemascope
- 32 channel audio support
- Dolby TrueHD capable
- Supports 8-channel LPCM, 192 kHz, 24-bit audio capability
- Supports DTS-HD Master Audio bitstream
- Supports Super Audio CD (DSD)
- Supports DVD audio
- Supports Blu-ray Disc and HD DVD audio and video
- Connector surface: gold-plated
- Color cable: black
- Hoods: Metallic housing
- Hoods: Metallic housing
- Shielding: Double shielding
- AOC - Active Optical Cable: yes
- Connector 1: HDMI type A, plug
- Connector 2: HDMI type A, plug
- HDMI Standard: Premium High Speed HDMI with Ethernet
- HDTV Resolution max.: 4096 x 2560 Pixel, 60Hz
- HDTV Standard: Ultra HD 4K
- Length: 30 m

Logistics						
	Number (pcs)	Weight (kg)	Depth (cm)	Width (cm)	Height (cm)	cm³
Packaging Unit Carton	16	16.00	45.00	34.00	28.00	42,840.00
Packaging Unit Inside	1	1.00	16.00	16.00	7.50	1,920.00
Packaging Unit Single	1	1.00	16.00	16.00	7.50	1,920.00
Net single without Packaging	1	0.93	16.00	16.00	7.50	1,920.00

More images:

