



Datasheet RS PRO WA22 Series Panel Mount Internally Threaded Connector

Stock No: 2107324



Product Details

The RS Pro WA22 series are a range of ruggedly built IP67 waterproof connectors, available in 3+PE or 6+PE configurations with internal or external threading. Versions are available for in-line cable to cable and for cable to panel connections with the plugs and receptacles being either male pins or female sockets. The WA22 series are also intermateable with similar designed connectors from other manufacturers.

Features and Benefits

- Threaded Coupling
- IP67
- Plastic
- 7 Poles
- Panel Mount Connector


Technical Specifications:

Material and spec		- 000
Number of contact	3+PE	6+PE
Contact diameter (mm)	ø2	Ø1.5
Rated voltage (AC.V)	400	250
Rated current (A)	16	10
Wire size (mm ² /AWG)	≤2. 5/14	≤0.75/18
Termination	Screw	Solder
Test voltage(AC.V)1min	2000	
Insulation resistance (M Ω)	2000	
Shell material	Nylon66, fire resistance: V-0	
Contact material	Brass with gold plating	
Temperature range	-40°C~+85°C	
Mating cycle	500	





Dimensional line drawings



Quality Standards





