



Search by part # or keyword

[Products](#)

[Industries & Solutions](#)

[Resources](#)

[Shop TE](#)

[Sign In](#)



Purchase items directly from TE.com

[Reliable Switching Devices](#) > [Switches](#) > [DIP & SIP Switches](#)

4-1825059-2

Alcoswitch DIP, DIP & SIP Switches, Switch, Gold Flash, Black, Polyphenylene Sulfide (PPS), Auto-Insertable, Sealed, 8 Switches



Alcoswitch | Alcoswitch DIP , Alcoswitch DIP ADF

TE Internal #: **4-1825059-2**
 TE Internal Description: **ADF08STTR04=DIP S,FLUSH,SMT-GW**
 Alias #: **ADF08STTR04**

Product Type : **Switch**
 Contact Mating Area Plating Material : **Gold Flash**
 Housing Color : **Black**
 Housing Material : **Polyphenylene Sulfide (PPS)**
 Auto-Insertable : **Yes**

[Digital Datasheet](#)

[ORDER SAMPLES](#)

[Compatible Parts & Tooling](#)

We are here to help!

Get in touch with our product experts.

	CHAT WITH US
	EMAIL US
	CALL US

Documents

Features

Product Compliance

Product Drawings

ADF08STTR04=DIP S,FLUSH,SMT-GW
[ADF08STTR04=DIP S,FLUSH,SMT-GW](#)
 English

CAD Files

PCB Design
[Download symbol & footprint \(SnapEDA\)](#)
[Download symbol & footprint \(Ultra Librarian\)](#)
 3D PDF
[3D_CVM_CVM_4-1825059-2_A.pdf](#)
 3D
 Customer View Model
[ENG_CVM_CVM_4-1825059-2_A.2d_dxf.zip](#)
 English
[ENG_CVM_CVM_4-1825059-2_A.3d_igs.zip](#)
 English
[ENG_CVM_CVM_4-1825059-2_A.3d_stp.zip](#)
 English

Datasheets &

[SWITCHES_CORE_PROGRAM_CATALOG](#)



Catalog Pages	ENG_CS_1308111-1_SWITCHES_CORE_PROGRAM_CATALOG_0308.pdf English
Product Environmental Compliance	MD_4-1825059-2_07292013657_dmtec ENG_PC_MD_4-1825059-2_B(969683).xlsx English MD_4-1825059-2_07292013657_dmtec ENG_PC_MD_4-1825059-2_B(396688).xml English
Please review product documents or contact us for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.	
Product Type Features	Product Type : Switch Sealed : Yes Switch Type : DIP Actuator Style : Flush, Slide
Configuration Features	Number of Switches : 8 Configuration (Pole-Throw) : Single Pole - Single Throw Number of Positions : 8
Electrical Characteristics	Voltage Rating (VDC): 5
Body Features	Actuator Color : White Seal Type : Tape
Contact Features	Contact Mating Area Plating Material : Gold Flash Auto-Insertable : Yes Contact Current Rating (A): 1 Contact Base Material : Copper Alloy Solder Tail Contact Plating : Nickel Contact Mating Area Plating Thickness (µin): 1.2
Termination Features	Termination Style : Outside L
Mechanical Attachment	Mounting Type : Surface Mount
Housing Features	Housing Color : Black Housing Material : Polyphenylene Sulfide (PPS) Centerline : 2.54 mm [.1 in]
Dimensions	Height : 3.5 mm [.138 in] Length : 22.3 mm [.878 in]

Usage Conditions	Operating Temperature Range (°C): -30 – 85
Industry Standards	UL Flammability Rating : UL 94V-0
Packaging Features	Packaging Quantity : 750 Packaging Method : Tape & Reel
Statement of Compliance	Statement of Compliance pdf


Also in the Series | [Alcoswitch DIP](#)



[DIP & SIP Switches \(256\)](#)



[Rotary Switches \(34\)](#)



[Switch Boots & Accessories \(1\)](#)

Also in the Series | [Alcoswitch DIP ADF](#)



[DIP & SIP Switches \(49\)](#)

