

Johanson Product Information for 4700BP14A0600001T

Johanson Company: Johanson Technology inc.

Deprecated P/N: 4700BP14A0600T

Datasheet Date: 03-26-2023

Description: Band Pass Filters, 603, 4400-5000MHz, 3W, 2.5dB, Ag/Pt (RoHS), 4.7GHz Band Pass Filter, EIA 0603, SMD, Low Loss and High Attenuation, 7" Reel Paper Tape

Life Cycle Stage: Active - Production

AEC Q200 Qualified: No

Schedule B: 8534.00.0085

Harmonization Code: 8534.00.00.85

ITAR: No

ECCN: EAR99

RoHS Compliance: Yes, RoHS 10/10

REACH: Yes

Country of Origin: TW

Product Family: Integrated Passive Components

Product Subfamily: Band Pass Filters

Termination: Ag/Pt (RoHS)

Marking: Special

Product Release Date: 21 October, 2019

Web Page Link:

<https://johansontechnology.com/band-pass-filters>

NCNR: No

Thickness (Max): 0.016

End Band (Min): 0.008

End Band (Max): 0.012

Standard Item: No

Lead Time Typical (Weeks)*:

*This can vary significantly so it is important to obtain a quotation with lead time for production planning purposes. 14

Length (Min): 0.057

Length (Max): 0.069

Width (Min): 0.025

Width (Max): 0.037

Packaging: 7" Reel Paper Tape

Packaging Qty: 4000

Operating Temp Range: -40°C to +85°C

Storage Temp Range (Packaged): +5°C to +35°C with RH 45% to 75%

Storage Temp Range (Non Operating): -40°C to +85°C