

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [5037630291](#)  
**Status:** **Active**  
**Overview:** [Pico-Lock Connector System](#)  
**Description:** 1.00mm Pitch, Pico-Lock PCB Header, Single Row, Right-Angle, Surface Mount, Gold over Nickel Plating, Positive Lock, 2 Circuits, Tape and Reel

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Product Specification PS-503764-001-001 (PDF)</a>
<a href="#">2D Drawing (DXF)</a>	<a href="#">Application Specification AS-503764-001-001 (PDF)</a>
<a href="#">2D Drawing DXF (PDF)</a>	<a href="#">Packaging Specification SPK-503763-001-001 (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">3D Model</a>	<a href="#">Product Literature (PDF)</a>
<a href="#">Product Specification 5037641001-PS-000 (PDF)</a>	

**Agency Certification**

UL E29179

**General**

Product Family	PCB Headers
Series	<a href="#">503763</a>
Application	Signal, Wire-to-Board
Overview	<a href="#">Pico-Lock Connector System</a>
Product Name	Pico-Lock
UPC	887191579337

**Physical**

Breakaway	No
Circuits (Loaded)	2
Circuits (maximum)	2
Color - Resin	Black
Durability (mating cycles max)	30
First Mate / Last Break	No
Flammability	SC-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	N/A
Lock to Mating Part	Yes
Mated Height	1.50mm
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Resin	High Temperature Thermoplastic
Net Weight	47.560/mg
Number of Rows	1
Orientation	Right Angle
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	1.00mm
Pitch - Termination Interface	1.00mm
Plating min - Mating	0.100µm
Polarized to Mating Part	Yes
Shrouded	Yes
Stackable	No
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Surface Mount

**Electrical**

Current - Maximum per Contact 1.5A



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2020)9139-DC (19  
Jan 2021)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[503763 Series](#)

**Mates With**

Pico-Lock Crimp Housing [503764](#) <br>Pico-Lock Cable Assembly [15131](#)

Voltage - Maximum

150V AC (RMS)/DC

**Material Info**

**Reference - Drawing Numbers**

Application Specification

AS-503764-001-001

Packaging Specification

SPK-503763-001-001

Product Specification

5037641001-PS-000, PS-503764-001-001

Sales Drawing

5037630000-SD-000

This document was generated on 02/24/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**