

Coaxial Cable Connector 11_MMCX-50-1-1/111_O

Description

Straight cable plug

Interface standards
SUHNER-MMCX



Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 6 GHz

Mechanical Data

Centre contact crimped
Outer contact crimped
Weight 0.0009 kg

Environmental Data

Operating temperature -55 °C to 155 °C
2011/65/EU (RoHS - including
2015/863 and 2017/2102) compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	Gold Plating (without Nickel underplating)
Body	Brass	Gold Plating (without Nickel underplating)
Insulator	PFA / PTFE	
Crimp ferrule	Brass	Gold Plating (without Nickel underplating)

Related Documents

Outline drawing DOU-00006970
Catalogue drawing DOU-00006168
Assembly instruction DOC-0000179110

Ordering Information

Bulk 100 pcs package 11_MMCX-50-1-1/111_OH
Single package 11_MMCX-50-1-1/111_OE

Additional Information

Suitable cables RG_178_B/U, RG_196_A/U, RG_196_A/U