

Between Series Adaptor 31_N-TNC-50-1/133_U

Description

Adaptor jack/jack
N jack (female) / TNC jack (female)

Interface standards
Series N - IEC 61169-16_MIL-STD-348A/304_CECC 22210
Series TNC - IEC 60169-17_MIL-STD-348A/313_CECC 22200



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	11 GHz
VSWR	DC - 7 GHz ≤ 1.06 + 0.12 f (GHz)
Frequency range	7 to 11 GHz
Return loss	≥ 10 dB

Mechanical Data

Number of matings	500
Weight	0.0302 kg

Environmental Data

Operating temperature 2011/65/EU (RoHS - including 2015/863 and 2017/2102)	-65 °C to 165 °C compliant
--	-------------------------------

Material Data

Interface - N jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Interface - TNC jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Related Documents

Catalogue drawing	DCA-00014590
-------------------	--------------

Ordering Information

Single package	31_N-TNC-50-1/133_UE
----------------	----------------------