


Non magnetic  
SMD-Tweezers




Model	Size	Description
-------	------	-------------



<b>SMD20SA</b> 4 70 020 00	115 mm 4 1/4"	Picking angle 30°, for Chip-components..
-------------------------------	------------------	--



<b>SMD21SA</b> 4 70 021 00	115 mm 4 1/4"	Picking angle 20°, for SOT-components.
-------------------------------	------------------	--



<b>SMD22SA</b> 4 70 022 00	115 mm 4 1/4"	Picking angle 90°, for Chip-components.
-------------------------------	------------------	---



<b>SMD23SA</b> 4 70 023 00	115 mm 4 1/4"	Picking angle 90°, for MELF's from 1,3 mm ø.
-------------------------------	------------------	--



<b>SMD24SA</b> 4 70 024 00	115 mm 4 1/4"	Picking angle 75°, for Mini MELF's from 1,3 mm ø.
-------------------------------	------------------	---



<b>SMD25SA</b> 4 70 025 00	115 mm 4 1/4"	Picking angle 20°, for Mini MELF's from 1,3 mm ø.
-------------------------------	------------------	---

## Description

## Size

## Model

Picking angle 75°, for Flatpacks up to max. 20 mm.

115 mm  
4 1/4"

**SMD26SA**  
4 70 026 00



Picking angle 75°,  
for diodes 0,8 mm ø.

115 mm  
4 1/4"

**SMD27SA**  
4 70 027 00

