

STANDARD 75 OHM COAX BNC TO BNC CABLES



- Van Damme UP-OFC 6.00mm Plasma Grade Standard 75 Ohm cable terminated with Van Damme 2GHz precision BNC connectors
- For analogue video use, also suitable for SMPTE 259M SDI digital video
- Exceptionally flexible cable
- Supplied with Orange strain relief boots
- Hand assembled in the UK
- RoHS Compliant

COMPONENT PARTS

Van Damme OFC 6.00mm Plasma Grade Standard 75 Ohm cable

Impedance at 10MHz 75 Ohms \pm 2

Attenuation

10 MHz	4.21 dB/100m
135 MHz	15.08 dB/100m
180 MHz	17.42 dB/100m

Van Damme Standard 75 Ohm BNC

- High quality 2GHz rated crimp BNC connector
- Turned nickel plated brass body, gold plated brass centre pin, PTFE insulator
- Meets the requirements of SMPTE 292M (1.5 Gb/s data rate)

PRODUCT CODES

Product Code	Description
110-062-000	Van Damme standard 75 BNC to BNC 1m
110-064-000	Van Damme standard 75 BNC to BNC 3m
110-065-000	Van Damme standard 75 BNC to BNC 5m
110-102-000	Van Damme standard 75 BNC to BNC 10m