

## SKINTOP® GMP-GL-M

SKINTOP® GMP-GL-M, glass fibre-reinforced counter nuts, for maximum mechanical stability, for locking in boreholes without thread



Good chemical resistance



Assembly time



Oil-resistant



Temperature-resistant



UV-resistant



Variety of approval certifications

### Benefits

Glass fibre-reinforced for maximum mechanical stability

Supporting surface for spanner means scratches on the housing are avoided

### Norm references / Approvals

UL File Nr. E79903

### Product Make-up

Metric connection thread acc. to DIN EN 60423

Basis for technical information DIN IEC 62444

### Note

Last Update (29.07.2020)

©2020 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## SKINTOP® GMP-GL-M

UL approval only when used with the UL-approved SKINTOP® polyamide cable glands

### Technical Data

|                        |  |
|------------------------|--|
| Classification ETIM 5: | ETIM 5.0 Class-ID: EC000940<br>ETIM 5.0 Class-Description: Locknut for cable screw gland |
| Classification ETIM 6: | ETIM 6.0 Class-ID: EC000940<br>ETIM 6.0 Class-Description: Locknut for cable screw gland |
| On request:            | Available without collar<br>(without surface for assembling tool)                        |
| Colour delivered:      | Silver grey (RAL 7001)<br>Light grey (RAL 7035)<br>Black (RAL 9005), UV-resistant        |
| Material:              | Polyamide, glass fibre-reinforced  |
| Temperature range:     | Fixed: -40 °C to +100 °C<br>Dynamic: -20 °C to +100 °C                                   |

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

**SKINTOP® GMP-GL-M**

| Article number                | Article designation / size | SW wrench size mm | Pieces / PU |
|-------------------------------|----------------------------|-------------------|-------------|
| SKINTOP® GMP-GL-M silver grey |                            |                   |             |
| 53119000                      | M 12 x 1,5                 | 17                | 100         |
| 53119010                      | M 16 x 1,5                 | 22                | 100         |
| 53119020                      | M 20 x 1,5                 | 27                | 100         |
| 53119030                      | M 25 x 1,5                 | 34                | 100         |
| 53119040                      | M 32 x 1,5                 | 41                | 100         |
| 53119050                      | M 40 x 1,5                 | 50                | 25          |
| 53119060                      | M 50 x 1,5                 | 60                | 25          |
| 53119070                      | M 63 x 1,5                 | 75                | 25          |
| SKINTOP® GMP-GL-M black       |                            |                   |             |
| 53119100                      | M 12 x 1,5                 | 17                | 100         |
| 53119110                      | M 16 x 1,5                 | 22                | 100         |
| 53119120                      | M 20 x 1,5                 | 27                | 100         |
| 53119130                      | M 25 x 1,5                 | 34                | 100         |
| 53119140                      | M 32 x 1,5                 | 41                | 100         |
| 53119150                      | M 40 x 1,5                 | 50                | 25          |
| 53119160                      | M 50 x 1,5                 | 60                | 25          |
| 53119170                      | M 63 x 1,5                 | 75                | 25          |
| SKINTOP® GMP-GL-M light grey  |                            |                   |             |
| 53119003                      | M 12 x 1,5                 | 17                | 100         |
| 53119013                      | M 16 x 1,5                 | 22                | 100         |
| 53119023                      | M 20 x 1,5                 | 27                | 100         |
| 53119033                      | M 25 x 1,5                 | 34                | 100         |
| 53119043                      | M 32 x 1,5                 | 41                | 100         |
| 53119053                      | M 40 x 1,5                 | 50                | 25          |
| 53119063                      | M 50 x 1,5                 | 60                | 25          |
| 53119073                      | M 63 x 1,5                 | 75                | 25          |

Last Update (29.07.2020)

©2020 Lapp Group - Technical changes reserved

 Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03\_16