


**manifold rail**  
**VABM-L1-10HW-G18-8-GR**  
 Part number: 573438



**Data sheet**

<b>Feature</b>	<b>Value</b>
Grid dimension	10.5 mm
Assembly position	Any
Max. number of valve positions	8
Corrosion resistance classification CRC	2 - Moderate corrosion stress
Storage temperature	-20 ... 60 °C
Authorisation	c CSA us (OL) c UL us - Recognized (OL)
Product weight	540 g
Auxiliary pilot air port 12/14	M5
Pilot exhaust port 82/84	M5
Pneumatic connection, port 1	G1/8
Pneumatic connection, port 2	M7
Pneumatic connection, port 3	G1/8
Pneumatic connection, port 4	M7
Pneumatic connection, port 5	G1/8
Materials note	Conforms to RoHS
Material manifold	Wrought Aluminium alloy