

prevoS1 blow gun with OSHA metal nozzle



Technical characteristics

Max operating pressure: 12 bar


Temperature: -15°C to +70°C

Construction: Polyamide composite body

Highlight: Compact

Connection: Built-in adaptor

prevoS1 coupler sold separately: ISI 06

	A (mm)	B (mm)	Blowing force (at 6 bar (g))	Dynamic pressure (at 10 mm at 6 bar (bar))	Air consumption (at 6 bar (Nm ³ /h))	Sound level (at 6 bar (dBA))	Parts Numbers
	180	97	248	2.3	13	85	IBG 06MTLH