

STANLEY®



FATMAX FCL-R (Alcalines) CROSS LEVEL – RED

Reach 15 m (50 m with cell)

Practical | 150° angle that allows for greater line return to the ceiling

Efficient | Pulsed mode for outdoor use with sensor cell (not supplied)

multipurpose | Successive projection of a horizontal and vertical line forming a cross

Résistant | Reinforced coating - IP54 protection

Practical | 1/4" and 5/8" thread

Secure | Lock compensator with on-off button

Supplied with 4 AA batteries, carrying case, wall mount and accessories

Laser Diode

Classe 2 – 620-680 nm

Accuracy

+/- 3 mm @ 10 m

Leveling range

+/- 4°



FMHT77585-1

3 253 561 775 857